Part Number : 5601240131
Product Description : DuraClik ISL Wire-to-Board Crimp Receptacle Terminal, Female, AVSS 0.30mm² Wire, Gold (Au) Plating
Series Number : 560124
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

5601240131_sd.pdf

Specifications

PK-560124-002-001.pdf

5601240131-000.pdf (Gold Plating)

Tooling Specifications

CS-560124-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	560124
Description	DuraClik ISL Wire-to-Board Crimp Receptacle Terminal, Female, AVSS 0.30mm² Wire, Gold (Au) Plating
Application	Automotive, Wire-to-Board
Product Name	DuraClik
UPC	889056303293

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	125V

Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	0.063/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.40mm
Wire Size (AWG)	N/A
Wire Size mm²	0.35

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
DuraClik ISL Single Row Receptacle Housings	560123

Application Tooling

Global

Description	Part Number
FA2 Mechanical Feed Crimp Applicator for 2.00mm Wire-to-Board DuraClik ISL Receptacle Terminals	638084400
FA2 Pneumatic Feed Crimp Applicator for 2.00mm Wire-to-Board DuraClik ISL Receptacle Terminals	638084410
Extraction and Activation Tool	638132700
Hand Crimp Tool for DuraClik ISL Receptacle Terminal, AVSS 0.30-0.35mm^2 Wire	638277800

Downloaded from Arrow.com.