

**Part Number :** [1300940235](#)

**Product Description :** Standard Duty Support Grip, Single Eye, Closed Mesh, Single Weave, Cable Diameter 19.05-25.15mm (.750-.990"), Approximate Break Strength 589.67kg (1300 lbs), Stainless Steel

**Series Number :** 130094

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 35032SS



---

## Documents and Resources


### Drawings

[PK-130227-004-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21   |
| REACH SVHC         | Not Reviewed per D(2025)7771-DC (04 Feb 2026)   |
| EU RoHS            | Compliant per EU 2015/863   |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

|              |   |
|--------------|---|
| Status       | Active  |
| Category     | Cable Grips   |
| Series       | 130094  |
| Description  | Standard Duty Support Grip, Single Eye, Closed Mesh, Single Weave, Cable Diameter 19.05-25.15mm (.750-.990"), Approximate Break Strength 589.67kg (1300 lbs), Stainless Steel |
| NEMA Rating  | NEMA 4  |
| Product Name | Standard Duty   |
| Type         | Support Grip  |
| UPC          | 78678809771   |

#### Physical

|                            |                            |
|----------------------------|----------------------------|
| Approximate Break Strength | 598.74kg (1320 lbs)        |
| Bale Length                | 0.203m (8.00")             |
| Body Style                 | Straight                   |
| Cable Diameter             | 19.05-25.15mm (.750-.990") |
| Color - Grommet            | N/A                        |
| Eye Type                   | Single                     |
| Gender                     | N/A                        |
| Material - Body            | N/A                        |
| Material - Grip            | Stainless Steel            |
| Mesh Length                | 0.356m (14.00")            |
| Net Weight                 | 588.000/g                  |
| Number of Holes            | N/A                        |
| O-Ring                     | No                         |

|             |     |
|-------------|-----|
| Thread Size | N/A |
|-------------|-----|

---

This document was generated on May 21, 2026