



Part Number : [1122190052](#)
Product Description : Woodhead ArcArrest
70° Angle Receptacle, Switch-Rated, 30.0A,
480V AC, 3-Pole+Ground, Insulator Keying
Position 4
Series Number : 112219
Status : Active
Product Category : Wiring Devices
Engineering Number : ARC30FAE03



Documents & Resources

Drawings
[Drawing 1122190052_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	112219
Description	Woodhead ArcArrest 70° Angle Receptacle, Switch-Rated, 30.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4
IP Rating	IP69K
NEMA Configuration	N/A
Product Family	Woodhead ArcArrest Connector System
Product Name	ArcArrest
Specialty	Switch-Rated
Type	Receptacle
UPC	78172559229

Agency

UL	E145923
----	---------

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	480V AC

Physical

Cord Type	N/A
Flange	Yes
Flip Lid	Yes
Gender	Female
Length	110.30mm (4.340")
Lighted Connector	No
Locking Blade	N/A
Net Weight	98.540/g
Poles	3

Receptacle Type	Single
Wire Size (AWG)	8 to 12

Mates With / Use With

Mates with Part(s)

Description	Part Number
Woodhead ArcArrest Plug with Handle, Drawplates, and Cap, Switch-Rated, 30.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4, Three Grommets Included	<u>1122191024</u>
Woodhead ArcArrest Plug with Handle and Cap, Switch-Rated, 30.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4, Three Grommets Included	<u>1122191038</u>

This document was generated on Sep 04, 2023