




BOTTOM VIEW



SIDE VIEW



ANGLED VIEW



Specifications			Notes	Revision History					
Description	Value	Unit		Version	Description		Date	Approved	
Directivity	Omnidirectional		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering		10/21/2013	J.S	
Technology	Electret Condenser								
Sensitivity	-44	(dB)							
Frequency Range	40 ~ 20,000	(Hz)							
Rated Voltage	2	(V)							
Output Impedance	2,200	(Ohm)							
Connection Method	PC Pins								
Voltage Range	1 ~ 10	(V)							
Max Rated Current	0.45	(mA)							
Minimum Signal to Noise Ratio	>60	(dB)							
Operating Temperature	-40 ~ +85	°C	 DB UNLIMITED	Drawn by	Date	Checked by	Date	Approved by	Date
Storage Temperature	-40 ~ +85	°C		A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
			Electret Condenser Microphone			MO064402-4			

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.