

No Image Available

No Image Available

172054 -5

Active

RoHS Compliant (Statement of Compliance)

- ? Connector
- ? Connector Type = Standard
- ? Mating Type = Receptacle
- ? Number of Positions = 5
- ? Terminate To Wire

[View all Features](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

? [JAPANESE \(1\)](#) (PDF, English)
 ? [JAPANESE \(2\)](#) (PDF, English)

[? REPRESENTATIVE TERMINALS AND CONNECTORS](#) (PDF, English)

? [AMP Mass - Termination "EI" Seires Connector](#) (PDF, English)

? [Terminating AMP MTEI Connector](#) (PDF, English)

? None Available

? None Available

List all Documents

? Product Line Information

? Tooling

- ? Product Type = Connector
- ? Connector Type = Standard
- ? Mating Type = Receptacle
- ? Number of Positions = 5
- ? PCB Retention Feature = No
- ? Wire Size (mm² [AWG]) = 28
- ? UL Recognized = Yes
- ? Comment = For replacement contacts see EI Series Connectors - Base part numbers 170204, 170205, 170262 and 170263.

? Centerline (mm [in]) = 2.50 [0.098]

? Contact Material = Phosphor Bronze

? Contact Mating Area Plating = Pre -Tin

? Housing Color = Green
 ? Housing Material = Nylon
 ? Housing Flammability Rating = UL 94V -0

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Terminate To = Wire

? Brand = AMP