

Relay socket - RIF-3-BSC/2X21 - 2900935

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://phoenixcontact.com/download>)



RIF-3... relay base, for octal relay with 2 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5



Key Commercial Data

Packing unit	1
GTIN	 4 046356 733021
GTIN	4046356733021
Custom tariff number	85366990

Technical data

Dimensions

Width	40 mm
Height	96 mm
Depth with retaining bracket	90 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (Depends on application/assembly)
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Input data

Protective circuit	depending on the selected input/suppressor modules
--------------------	--

Connection data, input side

Connection name	Input side
Connection method	Screw connection
Stripping length	8 mm

Relay socket - RIF-3-BSC/2X21 - 2900935

Technical data

Connection data, input side

Conductor cross section solid	0.14 mm ² ... 6 mm ²
Conductor cross section flexible	0.14 mm ² ... 4 mm ²
Conductor cross section AWG	26 ... 10

Connection data, output side

Connection name	Output side
Connection method	Screw connection
Stripping length	8 mm
Conductor cross section solid	0.14 mm ² ... 6 mm ²
Conductor cross section flexible	0.14 mm ² ... 4 mm ²
Conductor cross section AWG	26 ... 10

General

Nominal voltage U _N	250 V AC/DC
Nominal current I _N	max. 12.5 A (Depends on application/assembly)
Protective circuit	depending on the selected input/suppressor modules
Color	gray