

Shock protection - EMPPR (27X15) - 0829535

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Shock protection, Sheet, transparent, unlabeled, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm



Your advantages

- ✓ High level of mechanical and chemical stability
- ✓ Suitable for permanent outdoor use
- ✓ Stuck or snapped onto labeled CARRIER ... to protect the labeling
- ✓ Extremely thick, yet flexible and transparent shock protection

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 046356 614931
GTIN	4046356614931
Weight per Piece (excluding packing)	0.020 g
Custom tariff number	39204910
Country of origin	Germany

Technical data

Dimensions

Length (b)	15 mm
Width (a)	27 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 70 °C
---------------------------------	------------------

Shock protection - EMPPR (27X15) - 0829535

Technical data

Ambient conditions

Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in a cool and dry place is recommended.
--------------------------------	---

General

Color	transparent
Components	Silicone-free
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	snapped into marker carrier

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 11.0	24292214
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 4.0	EC002848
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

