


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		H3	REVISED PER ECR-19-014862	25SEP2019	LZ	TD




- 1 CONTINUOUS STRIP ON REELS.
- 2 TIN PLATE 0.00381 [.000150] MIN OVER 0.00254 [.000100] MIN THK COPPER OR TIN PLATE 0.00381 [.000150] MIN OVER 0.00127 [.000050] MIN THK NICKEL.
- 3 FEED IS 7.92±0.076 [.312±.003]
- 4 OPTIONAL ID MARK, LOCATION APPROX AS SHOWN.
- 5 REELED WITH INTERLEAVING PAPER.
- 6 LOOSE PIECE
- 7 LOOSE PIECE CUT-OFF DIMENSION
- 8 REEL PULL DIRECTUON REF TO FIGURE 318.
- 9 REEL PULL DIRECTUON REF TO FIGURE 918.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm[INCHES]



MATERIAL
BRASS

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.25 [.010]
3 PLC ± -
4 PLC ± -
ANGLES ± -

2

DWN JR RUTH 30NOV00

CHK MS FEHER 30NOV00

APVD G PORTA 30NOV00

PRODUCT SPEC

APPLICATION SPEC

114-2115

WEIGHT -

CUSTOMER DRAWING

NAME

TE Connectivity

TAB, FASTON,

PC BOARD,

6.35 [.250] SERIES

SIZE A3 CAGE CODE 00779 DRAWING NO C-63986 RESTRICTED TO -

SCALE 8:1 SHEET 1 OF 1 REV H3