



Part Number : 1301080301

Series Number : 130108

Product Category : Lamps and Lights

Product Description : Industrial Duty LED Tube Light, 72W, Cord Type 16/3 SOOW, 7.62m (25.0') Cord Length, 1.22m (4.0') Lamp Length, with 0.178m (7.00") Feed Thru Cord Length

Status : Active

Engineering Number : 2001LED

Documents & Resources

Drawings
Drawing 1301080301_sd.pdf

Specifications
Product Specification PS-130108-003-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130108
Description	Industrial Duty LED Tube Light, 72W, Cord Type 16/3 SOOW, 7.62m (25.0') Cord Length, 1.22m (4.0') Lamp Length, with 0.178m (7.00") Feed Thru Cord Length
NEMA Configuration	NEMA 5-15
Product Family	Wide-Area Lighting Products
Product Name	Industrial Duty
Type	Wide Area Lamps
UPC	78172546821

Agency

UL	E174254
----	---------

Electrical

Lamp Wattage - Maximum	72W
Lumens	7200
On/Off Switch	No
Voltage (Fixture) - Maximum	120/277VAC 50/60 HZ

Physical

Bulb Type	T10 LED - 5500K
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	0.178m (7.00")
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	16/3 SOOW
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	Yes
Guard Type	Clear Butyrate
Height	101.60mm (4.000")

Lamp Type	LED
Length	1.22m (4.0')
Material - Guard	Butyrate
Mounting Style	Straps
Net Weight	8719.980/g
Outlet	Feed-Through
Packaging Type	Carton
Socket Construction	Rubber Molded

This document was generated on Jul 03, 2024