

NetManager™ High Capacity Horizontal Cable Managers

- Innovative inset fingers slope inward toward back of managers offering unobstructed access to network cabling for easier moves, adds, and changes
- Large front finger openings easily accommodate Category 6 and 10 GbE cables, speeding installation and reducing maintenance costs
- Rear cable management finger spacing utilizes open D-rings for greater accessibility
- Can be used to create large capacity horizontal pathways for routing cable
- Patented front and rear dual hinged cover allows cable access without removing cover
- Curved surfaces maintain cable bend radius
- Pass-through holes allow for front to rear cabling
- Built in cable retainers hold cable in place for easy moves, adds, and changes
- Mount to 19" EIA racks and cabinets
- Covers, #12-24 and M6 mounting screws included
- Design fits flush to the front of the NetRunner® High Capacity WMPVHCF45E and WMPVHC45E Vertical Managers



NM2



NMF2



NMF3



NMF4



NM1B



NM2B



NM3B



NM4B

Part Number	Part Description	No. of Rack Spaces [^]	Std. Pkg. Qty.
-------------	------------------	---------------------------------	----------------

19" High Capacity Manager, Front and Rear

NM1	Horizontal Cable Manager High Capacity Front and Rear 1 Rack Unit. 1.7"H x 19.0"W x 13.1"D (44mm x 482mm x 332mm).	—	1
NM2	Horizontal Cable Manager High Capacity Front and Rear 2 Rack Units. 3.5"H x 19.0"W x 13.1"D (88mm x 482mm x 332mm).	—	1
NM3	Horizontal Cable Manager High Capacity Front and Rear 3 Rack Units. 5.2"H x 19.0"W x 13.1"D (133mm x 482mm x 332mm).	—	1
NM4	Horizontal Cable Manager High Capacity Front and Rear 4 Rack Units. 7.0"H x 19.0"W x 13.1"D (177mm x 482mm x 332mm).	—	1

19" High Capacity Manager, Front Only

NMF1	Horizontal Cable Manager High Capacity Front Only 1 Rack Unit. 1.7"H x 19.0"W x 6.2"D (44mm x 482mm x 157mm).	1	1
NMF2	Horizontal Cable Manager High Capacity Front Only 2 Rack Units. 3.5"H x 19.0"W x 6.2"D (88mm x 482mm x 157mm).	2	1
NMF3	Horizontal Cable Manager High Capacity Front Only 3 Rack Units. 5.2"H x 19.0"W x 6.2"D (133mm x 482mm x 157mm).	3	1
NMF4	Horizontal Cable Manager High Capacity Front Only 4 Rack Units. 7.0"H x 19.0"W x 6.2"D (177mm x 482mm x 157mm).	4	1

Accessories

NM1B	Front to rear pass through blanking panel for NetManager™ High Capacity Horizontal Cable Managers, NM1 and NMF1.	—	1
NM2B	Front to rear pass through blanking panel for NetManager™ High Capacity Horizontal Cable Managers, NM2 and NMF2.	—	1
NM3B	Front to rear pass through blanking panel for NetManager™ High Capacity Horizontal Cable Managers, NM3 and NMF3.	—	1
NM4B	Front to rear pass through blanking panel for NetManager™ High Capacity Horizontal Cable Managers, NM4 and NMF4.	—	1

[^]One rack space = 1.75" (44.5mm).
All product color is black.