



Part Number : [1301370223](#)
Product Description : Watertite GFCI Multiple
Outlet FD Box, (1) NEMA 5-15 Duplex with Flip Lids,
30.48m (100.0') Cord Length 14/3 SOOW Cord, NEMA
5-15 Watertite Plug
Series Number : 130137
Status : Active
Product Category : Power Distribution
Engineering Number : 3301GFD143



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Relevant

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Power Distribution
Series	130137
Description	Watertite GFCI Multiple Outlet FD Box, (1) NEMA 5-15 Duplex with Flip Lids, 30.48m (100.0') Cord Length 14/3 SOOW Cord, NEMA 5-15 Watertite Plug
Enclosure Rating	NEMA 4X
NEMA Configuration	NEMA 5-15
Product Name	Watertite
Type	GFCI Multiple Outlet Box
UPC	78678809449

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	No
Voltage - Maximum	120V

Physical

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	F3 3/4"
Cord Length	30.48m (100.0')
Cord Type	14/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Nylon
Mounting Style	Portable

Net Weight	1.000/kg
Number of Receptacles	1
Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on Sep 22, 2025