

Pluggable Screw Terminal Block

180° Wire Entry

Specifications:

| | |
|-------------------------------|---|
| Application | Used with 5mm socket available with Sonalert® Solution models. |
| Electrical | Max Voltage: 300V Max Current: 15 Amp |
| Screw Terminal | Tightening Torque: 8 in-lbs |
| Connection strength | Minimum of 5 lbs to remove pluggable screw terminal block from socket of Sonalert device. |
| Operating Temperature | Max 110°C |
| Material | Housing: UL94V0 Polymide (Color Black) Screw: Steel / Zinc chromate |
| Wire Range | 12 to 26 AWG |
| Wire Strip Length | 1/4 inch or 6mm |
| Dimensional Tolerances | 1 place = $\pm .3$ mm 2 places= $\pm .01$ inch or .13 mm 3 places= $\pm .005$ inch or .038 mm |

Dimensions: Inches (mm)**Flame Retardant** **RoHS Compliant**