


Data Sheet | Item Number: 793-608/000-012

WMB marking card; as card; MARKED; 101 ... 150 (2x); not stretchable; Vertical marking; snap-on type; orange

<https://www.wago.com/793-608/000-012>



Color: ■ orange

Similar to illustration

Technical data

Marking method	Thermal transfer
Marking	101 ... 150
Marking (number)	2
Marking direction	Vertical marking
Marking color	black
Marking type	Numbers
Marking layout	Consecutive numbers per strip
Delivery form	Marker card
Delivery form configuration	10 strips with 10 markers per card
Flammability class per UL94	V2

Physical data

Marker/strip width	5 mm
Marker width	5 mm

Mechanical data

Smear resistance	EN 60998-1:2004
------------------	-----------------

Material data	
Color	orange
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	9 g
Fire load	0.27 MJ

Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	50 (5) pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918113328
Customs tariff number	49119900000

Product Classification	
UNSPSC	55121731
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 10.0	EC000761
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 793-608/000-012	

Installation Notes

Application



Separating a strip from the WMB or WMB marker card.

Stretching a WMB marker strip.

Separating an individual marker from the WMB marker strip – for larger terminal blocks.

Snapping a marking strip into the marker slot.

Marking



Snapping a WMB marker strip into the marker slot of the double marker carrier.

Snapping a marking strip into the marker slot.