Datasheet for part number DEMM-9S-N-A197

Our Catalog Part Number: DEMM-9S-N-A197
Our Global Manufacturing Part Number: 051529-0124
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M

Product Datasheet	
General	D*M High reliable D-Sub Connectors
Wire Gauge Range AWG	AWG 20-28
Mating Cycles	500
Contact Arrangement	9 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	7.5 milli Ohm max
Operating Temperature	-55°/+150°
Salt Spray Test	48 hours {96 Hrs for Stainless Steel}
Shell Material	Steel
Shell Finish	Pure tin over nickel
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Socket
Contact Type	Straight PCB
Contact Material	copper alloy
Contact Finish	50 microinch gold over 40 microinch nickel
Hardware	.120" (3,05mm) Through Hole

Specifications and dimensions subject to change.

Downloaded from Arrow.com.