
Part Number : 190070015
Product Description : Flag InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2) Wire, Box, Tab 4.75 x 0.81mm, Carton
Series Number : 19007
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : AA-2223



Documents and Resources

Drawings

190070015_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-008-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19007
Description	Flag InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2) Wire, Box, Tab 4.75 x 0.81mm, Carton
Product Name	InsulKrimp
Type	Flag Terminal
UPC	800753031623

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-2

Downloaded from Arrow.com.

Gender	Female
Glow-Wire Capable	Yes
Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.052/g
Orientation	Flag
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	4.75mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	4.44mm max.
Wire Size (AWG)	18, 20, 22

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Flag Insulkrimp Quick Disconnect Terminals, 22-14 AWG	640014100
Crimp Head for the AT-200 Pneumatic Hand Tool	640054100

Downloaded from Arrow.com.