

Cable duct - CD-HF 40X40 - 3240348

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable duct for installation and mounting in control cabinets, light gray, halogen-free, comprising upper part and mounting base, width: 40 mm, height: 40 mm, length: 2000 mm

Your advantages

- ✓ Predetermined breaking point enables tool-free, burr-free removal of bars
- ✓ Fast and seamless creation of T and cross connections by means of an additional predetermined breaking point in the cable duct base
- ✓ The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- ✓ Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- ✓ Cover is securely held in place for both horizontal and vertical mounting



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	25 pc
GTIN	 4 046356 508339
GTIN	4046356508339
Weight per Piece (excluding packing)	760.000 g
Custom tariff number	39259020
Country of origin	Germany

Technical data

Dimensions

Length (b)	2000 mm
Width (a)	40 mm
Height (c)	40 mm

Cable duct - CD-HF 40X40 - 3240348

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
---------------------------------	------------------

General

Color	light grey RAL 7035
Components	halogen-free
Material	PC/ABS
Flammability rating according to UL 94	V0
Nominal cross section	749 mm ²

Standards and Regulations


Halogen-free	yes
Connection in acc. with standard	CSA

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Base perforation according to DIN EN 50085

Classifications

eCl@ss

eCl@ss 10.0.1	27400703
eCl@ss 11.0	27400703
eCl@ss 4.0	27140600
eCl@ss 4.1	27140600
eCl@ss 5.0	27140600
eCl@ss 5.1	27140600

Cable duct - CD-HF 40X40 - 3240348

Classifications

eCl@ss

eCl@ss 6.0	27400700
eCl@ss 7.0	27400703
eCl@ss 9.0	27400703

ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000012
ETIM 4.0	EC000012
ETIM 6.0	EC000012
ETIM 7.0	EC000012

UNSPSC

UNSPSC 6.01	30101815
UNSPSC 7.0901	30101815
UNSPSC 11	30101815
UNSPSC 12.01	30101815
UNSPSC 13.2	39131712
UNSPSC 18.0	39131712
UNSPSC 19.0	39131712
UNSPSC 20.0	39131712
UNSPSC 21.0	39131712

Approvals

Approvals

Approvals

CSA / UL Recognized / VDE Zeichengenehmigung / EAC

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	248269
-----	---	---	--------

Cable duct - CD-HF 40X40 - 3240348

Approvals

UL Recognized



<http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm>

FILE E 328576

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

40028972

EAC



RU C-
DE.PB68.W.00513

Accessories

Accessories

Cover

Cover profile - CD-HF COVER 40 - 3240371



Cover for cable duct, light gray, halogen-free, width: 40 mm, length: 2000 mm

Filler plug

Fastening clip - RVT-PA 4 - 3240498



Plastic body-bound rivet, for hole diameter of 4 mm and a material thickness of 1.5 ... 6 mm

Fastening clip - RVT-PA 6 - 3240499



Plastic body-bound rivet, for hole diameter of 6 mm and a material thickness of 1.5 ... 6 mm

Cable duct - CD-HF 40X40 - 3240348

Accessories

Riveting tools

Tool - UNIFOX-RVT P 4 - 1212478



Rivet setting tool, for use with RVT-PA 4 plastic body-bound rivets

Tool - UNIFOX-RVT P 6 - 1212509



Rivet setting tool, for use with RVT-PA 6 plastic body-bound rivets

Universal wire retaining clip - CD WR - 3240284



Universal wire holding bracket, perforated, for wiring channels
