
Specifications



Photo is representative





Eaton LD1-101-R

Eaton LD inductor, 100 uH, 0.36 A Irms, 0.45 A ISAT, 1720 mΩ resistance, SMT mounting, Ferrite, 2-pins, 2000 qty.

General specifications	
PRODUCT NAME	Eaton LD1 inductor
CATALOG NUMBER	LD1-101-R
UPC	051712244978
PRODUCT LENGTH/DEPTH	4.8 mm
PRODUCT HEIGHT	3.5 mm
PRODUCT WIDTH	4.3 mm
PRODUCT WEIGHT	0.0004 lb
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.36 A
ISAT	0.45 A
PACKAGE QUANTITY	2000
MATERIAL	Ferrite
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	1720 mΩ
SERIES	LD

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - LD1-101-R Eaton LD metalized drum core power inductors data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.