# Datasheet for part number DB-25S-1-A-5-N-A191-A197

| Our Catalog Part Number: DB-25S-1-A-5-N-A191-A197 |
|---|
| Our Global Manufacturing Part Number: 121073-3235 D |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: ORIGINAL D |

| Product Datasheet | |
|---|---|
| General | Standard D-Subminiature |
| Wire Gauge Range AWG | AWG 20-28 |
| Mating Cycles | 200 |
| Dielectric Withstanding Voltage | 1200 VAC at sea level |
| Current Rating | 7.5 A at 85°C / 5 A at 105°C |
| Contact Resistance | 10 milli Ohm max |
| Operating Temperature | -55°/+125° |
| Salt Spray Test | 20 hours |
| Shell Material | steel |
| Shell Finish | tin |
| Insulator Material | Thermoplastic, type PCT UL 94V-0 |
| Insulator Color | black |
| Contact Arrangement | 25 contacts size 20 |
| Gender | Socket |
| Contact Type | turned |
| Contact Material | copper alloy |
| Contact Finish | gold over nickel (Performance Class 2) |
| Contact Termination | Right angled solder |
| Termination Direction | contact termination at short side of trapezoid (Standard) |
| Mounting Methode | Plastic bracket with 0,120‴ (3,05mm) Through Hole |

Specifications and dimensions subject to change.



Downloaded from Arrow.com.