



Part Number : [1300980166](#)
Product Description : MAX-LOC Strain Relief
Cord-Sealing Grip, 1" NPT, Straight Male,
Cable Diameter 22.23-25.40mm (.875-1.000")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Number : 5560



Documents & Resources

Drawings
[1300980166_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2020)4578-DC (25 June 2020)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, Straight Male, Cable Diameter 22.23-25.40mm (.875-1.000")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872135

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	22.23-25.40mm (.875-1.000")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	0.074/kg
Number of Holes	1
O-Ring	No
Thread Size	1" NPT

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1" NPT	<u>1300990145</u>
MAX-LOC Gasket Sealing Ring, 1" NPT, Black	<u>1300990151</u>
MAX-LOC O-Ring, 1" NPT	<u>1301800334</u>

This document was generated on Apr 22, 2025