

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
MINNEAPOLIS, MINN.

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

WZ-2RW822-A2

AVF2000

WZ-2RW822-A2
PAGE 1 OF 1

M

DRAWING
NUMBER

13

ISSUE

REPLACES

RELEASE NO.

CHECK

18 FEB 06

RJ

CHECK

21 SEP 62

CHECK

21 SEP 62

DAW

30 NOV 94

CHECK


19 MAY 62

GCH

19 MAY 62

DAW

30 NOV 94



NOTE -



MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE - - - - - 6 OZ MAX

RELEASE FORCE - - - - - 1 1/2 OZ MIN

DIFFERENTIAL TRAVEL - - - - - .003 - .020

OVERTRAVEL - - - - - .094 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N C

-L74- 15 A-125, 250, OR 480 VAC; 2A-600 VAC
1/2 A-125 VDC; 1/4 A-250 VDC
1/8 HP-125 VAC; 1/4 HP-250 VAC

-L288-

-L306-

-L315-



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .076 LB

FORMTEK

TO-50376

DRAWN

19 MAY 62