Part Number : 190020034
Product Description : Avikrimp Fully Insulated Quick Disconnect, Female, for 16-14 AWG Wire, Carton
Series Number : 19002
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : BB-5277



Documents and Resources

Drawings

190020034_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

PS-19902-014-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19002
Description	Avikrimp Fully Insulated Quick Disconnect, Female, for 16-14 AWG Wire, Carton
Product Name	Avikrimp
Type	Standard Quick Disconnect
UPC	800753027541

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	300V

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully

Downloaded from Arrow.com.

Insulation	Nylon (PA)
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.764/g
Orientation	Straight
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	2.79mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	3.94mm max.
Wire Size (AWG)	14, 16
Wire Size mm^2	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp Female Fully Insulated Quick Disconnect Terminals, 16-14 AWG	640011100
Crimp Head for the AT-200 Pneumatic Hand Tool	640051100

Downloaded from Arrow.com.