

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2014/07/31	Cary	Change To Rev. A


ALTW
CONFIDENTIAL
2014-07-31
R&D DEPT.


ALTW
DCC. DEPT.
CONFIDENTIAL
2014.08.12
ISSUED






RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE IS ±0.05







Notes:
* (QC) Important Dimension To Check.
* Waterphoof Rate: IP68(mating)
  IM Depth Of Water In 24 Hours.
* Housing: High temperature thermoplastic.
  UL94V-0, color is natural white.
* Terminal: Copper Alloy,Gold plated on contact area.
* Solder Peg: Copper Alloy,Tin plated over Nickel.
* Current Rating: 5A maximum.
* Voltage Rating:250V DC/AV maximum.
* Operating Temperature: -40~+105℃

UNIT:mm
TOLERANCE ±0.5mm

TITLE: SSL1.2 2P R/A SMT JACK CONN.
SCALE 3:1 | SIZE A4 | SHEET 1 OF 2
REV. A | WC-REV. A.4 | (QC):Inspection item


Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
SSL12-J2D00-000001	Cary_liu	2014-07-31
DWG NO: SSL12-J2D00-000001	CHECKED BY: Fisher	DATE: 2014-07-31
CUSTOMER: ALTW	APPROVED BY: Jerry	DATE: 2014-07-31

FMW10702-01-02A1

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Downloaded from Arrow.com.



UNIT: mm	TITLE: SSL1.2 2P R/A SMT JACK CONN.	Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO: SSL12-J2D00-000001	DRAWN BY: Cary_liu	DATE: 2014-07-31
TOLERANCE ±0.5mm	SCALE: 3:1 / SIZE: A4 / SHEET: 2 OF 2		DWG NO: SSL12-J2D00-000001	CHECKED BY: Fisher	DATE: 2014-07-31
	REV.: A / WC-REV.: A.4 / QC: Inspection item		CUSTOMER: ALTW	APPROVED BY: Jerry	DATE: 2014-07-31

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Downloaded from Arrow.com.