




## NOTES:

1. CRIMP CONTACTS SUPPLIED UNASSEMBLED AND WITHOUT EPOXY BACKING.
2. REFER TO DRAWING HPSFMISTD FOR CONTACT PATTERNS.
3. HEX-NUT TORQUE: 10-12 IN-LB.
4. DIMENSIONS ARE REFERENCE ONLY, IN INCHES [mm], WITHIN  $\pm 0.015$  UNLESS OTHERWISE NOTED.

**CRIMP CONTACTS**



SF7980-18PG-300 SHOWN


**FACE VIEW**  
SF7982-18PG-300 SHOWN


MAXIMUM PANEL THICKNESS

**SOLDER CONTACTS**

SF7982-18PG-300 SHOWN

**RECOMMENDED PANEL CUT-OUT****PC TAIL CONTACTS**



SF7984-18PG-3ES SHOWN

**PANEL-MOUNT CONNECTOR PART NUMBERS:****S F 7 9 8 X - X P G - 3XX**

EPOXY BACKING:  
3ES = WITH EPOXY  
300 = WITHOUT EPOXY

# OF CONTACTS: 9 - 18

CONTACTS STYLE:  
0 = CRIMP  
2 = SOLDER  
4 = PC TAIL


**WIRING END**  
SF7982-18PG-300 SHOWN


**CUSTOMER APPROVAL**

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT / INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: \_\_\_\_\_  
DATE: \_\_\_\_\_

0A	PNK	1-30-18	DRAWING CREATED PER PDR17011
REV.	INIT.	DATE	DESCRIPTION
ORIG. DRAWN BY: DATE: PNK 1-30-18			CHECKED BY:
APPROVED BY:			TITLE: <b>CONXALL</b> 601 E. WILDWOOD VILLA PARK, IL 60181
SCALE NTS	SIZE B	SHEET 1 OF 1	CUSTOMER: <b>PANEL-MOUNT CONNECTOR</b> (9-18) #26 PIN CONTACTS SHIELDED MINI-CON-X STANDARD PRODUCT
> = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX		FILE: SF798X-XPG-3XX_CD	PART NUMBER: SF798X-XPG-3XX
		DIRECTORY: SLW	REV 0A

**RoHS COMPLIANT**