

UK Computer Power Cord, BS1363 to C13 - 10A, 250V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P056-006-10A



UK computer power cord connects your computer or peripheral with a C14 inlet to any grounded AC power outlet that accepts BS1363 plugs.

Features

**UK IEC Power Cord Connects Computers, Servers and Other Network Devices**This BS1363 to C13 UK computer power cord is designed for small data center or office workstation applications that do not require a heavy-gauge connection. The cable can be used to connect a computer, server or drive to a BS1363 wall outlet, UPS system or PDU or replace or upgrade a worn-out or lost power cable. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332190796
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	UK
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Highlights

- BS1363 to C13 cable for powering computers, servers and other network devices
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing UK computer power cable

Applications

- Connect devices like computers, monitors and printers to a PDU up to 6 ft. (1.8 m) away in your home or office workstation
- Extend an existing power connection up to 6 ft. (1.8 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P056-006-10A BS1363 to C13, UK IEC Power Cable, 6 ft. (1.8 m), Black

Cable Jacket Rating	VW-1
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	7.09 x 7.87 x 0.50
Shipping Dimensions (hwd / cm)	18.01 x 19.99 x 1.27
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	BS1363 UK PLUG
Side B - Connector 1	IEC-320-C13
<b>FEATURES &amp; SPECIFICATIONS</b>	
High Voltage	Yes
Locking Plug	No
Antibacterial	No
Angled Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL Listed; cUL Listed
Product Compliance	CE (Europe); REACH; RoHS; UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.