Copyright FCI.

PRODUCT NUMBER	PITCH
V5xx51x400J0G	5.08 mm





SECTION P-P

Material:
- Item ⓐ Clamp: Brass Ni plated
- Item ⓑ Terminal(housing): Thermoplastic (UL94V-0)
- Item ⓒ Terminal(cover): Thermoplastic (UL94V-0)
- Item ⓓ Pin: Brass,Tin plated.
- Item ⓔ Terminal screw: Steel Zinc plating solt "-"type M3
- Item ⓕ Terminal(track): Thermoplastic (UL94V-0)

Electrical: cULus
- Voltage rating:300V
- Current rating: 12A
- Wire range:
- Solid wire(AWG):12-30
- Stranded wire(AWG):12-30
- Torque(Lb-In): 4.4
- Screw:M3
- Wire strip length: 6-7 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:

DIMENSION

Dim A	Nx5.08+1.52
Dim B	(N-1)x5.08+5.48
Dim C	(N-1)x5.08

N=Number of poles

Poles	Tolerance
2P-6P	±0.20
7P-12P	±0.25
13P-18P	±0.30
19P-24P	±0.40

PART NO.: V5 xx 51 x 4 00J0 G

Solid block
No. of poles
02 2 poles
03 3 poles
... ...
24 24 poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

| | | |