


Connectors > PCB Connectors > PCB Headers & Receptacles

1554458-2 ACTIVE

PCB Mount Header, Horizontal, Wire-to-Board, 33 Position, 2.8 mm [.11 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, Sealable, Black



TE Internal #: 1554458-2
TE Internal Description: 33POS,1.0X0.64,TAB HSG ASSY,SLD

Connector System : Wire-to-Board
Number of Positions : 33
Centerline (Pitch) : 2.8 mm [.11 in]
Sealable : Yes
PCB Mount Orientation : Horizontal

Add to List | Similar Products |
Digital Datasheet

GET FREE SAMPLES

Compatible Parts & Tooling

DocumentsFeaturesProduct Compliance

Product Drawings

33POS,1.0X0.64,TAB HSG ASSY,SLD
Japanese

CAD Files

3D PDF
3D_CVM_CVM_1554458-2_A.pdf
3D
Customer View Model
ENG_CVM_CVM_1554458-2_A_2d_dxf.zip
English
ENG_CVM_CVM_1554458-2_A_3d_igs.zip
English
ENG_CVM_CVM_1554458-2_A_3d_stp.zip
English

Product Specifications

Product Specification
JPN_SS_108-76718_A2.pdf
Japanese

THIS PART IS OUT OF STOCK

Similar Parts In Stock

Automotive Terminals, Receptacle, Mating Tab Width .039 in [1 mm]...

TE Part #: 1554723-1

View Product

Housing for Female Terminals, Wire-to-Wire, 18 Position, .138 in [3.5...

TE Part #: 1-2112780-9

View Product

We are here to help!
Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

Compatible Parts

Filter By Specification

MATING

1554461-2

Housing for Female Terminals, Wire-to-Board, 33 Position, .11 in [2.8...

Non-Stocked

VIEW PRODUCT

Products with Similar Specs


View All Similar Products

THIS PRODUCT

AUTOMOTIVE HEADERS

1554458-2

PCB Mount Header, Horizontal, Wire-to-Board, 33 Position, 2.8 mm...



Non-Stocked


Connector System : Wire-to-Board
Number of Positions : 33
Centerline (Pitch) : 2.8 mm
Sealable : Yes
PCB Mount Orientation : Horizontal

TOP RESULTS

AUTOMOTIVE HOUSINGS

3-2112780-7

Housing for Female Terminals, Wire-to-Board, 18 Position, .137 in [3.5...




Non-Stocked

Connector & Housing Type : Housing for Female Terminals
Mating Tab Width : 1.2 mm, 2.8 mm
Connector System : Wire-to-Board
Number of Positions : 18
Centerline (Pitch) : 3.5 mm

AUTOMOTIVE HOUSINGS

3-2112780-6

Housing for Female Terminals, Wire-to-Board, 18 Position, .137 in [3.5...




Non-Stocked

Connector & Housing Type : Housing for Female Terminals
Mating Tab Width : 1.2 mm, 2.8 mm
Connector System : Wire-to-Board
Number of Positions : 18
Centerline (Pitch) : 3.5 mm

AUTOMOTIVE HOUSINGS

2-2112780-6

Housing for Female Terminals, Wire-to-Board, 18 Position, .137 in [3.5...



Non-Stocked

Connector & Housing Type : Housing for Female Terminals
Mating Tab Width : 1.2 mm, 2.8 mm
Connector System : Wire-to-Board
Number of Positions : 18
Centerline (Pitch) : 3.5 mm

Customers Also Bought



TE Part #: 2315573-1
Housing for Female Terminals, 14 Position...

View Product



TE Part #: 3-967618-2
PCB Mount Header, Vertical, Wire-to-Board, 18 Position...

View Product



TE Part #: 967618-3
PCB Mount Header, Vertical, Wire-to-Board, 18 Position...

View Product



TE Part #: 967618-4
PCB Mount Header, Vertical, Wire-to-Board, 18 Position...

View Product