


10- $\varnothing$ 0.90 [0.035]
 2- $\varnothing$ 1.60 [0.063]
 3.60 [0.142]
 LOCATE HOLES
 $\varnothing$ 0.13 [0.005]
 POSITION ARE
 BASIC

3 LAYOUT
 BOARD
 (TOP VIEW)




CONTACT: PHOSPHOR BRONZE
PLATING:REFER TO PART NUMBER FOR GOLD
THICKNESS ON MATING SURFACE
50u" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100u" [2.54 MICRONS]
MIN. MATTE TIN OR GOLD FLASH OVER TAILS

SHIELD: BRASS WITH NICKEL PLATING.

AMPHENOL PART NUMBER: RJE29-188-1XX0

1 = 06u" GOLD
2 = 15u" GOLD
3 = 30u" GOLD
4 = 50u" GOLD

HOUSING OPTION:
5 = RED(PANTONE #032C), WITHOUT FLANGES
6 = BLUE(PANTONE #285C), WITHOUT FLANGES



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP