
Product information
GDME LED 24 YE

Industrial Connecting Solutions:Rectangular Connectors:Valve Connectors (Type A -B -C):Type A:Field Attachable Valve Connectors:Electronic inserts for GDME:GDME LED 24 YE

https://catalog.beldensolutions.com:443/link/57078-24228-256261-256266-256270-276215-24315-35669/en/conf/uistate

Name	GDME LED 24 YE
	function indicator (LED) with freewheeling diode
Delivery informations	
Availability	available
Product description	
Description	function indicator (LED) with freewheeling diode
Type	GDME LED 24 YE
Order No.	831 863-001
Standard	DIN EN 175 301-803-A
Construction type	A
Description of Wiring	
LED color	LED yellow
Technical data	
Rated voltage	AC/DC 24 V
Rated current	8 A
Environmental conditions	
Temperature range	-40 °C to +110 °C
Packing unit	
Packaging unit	50 pieces
Picture	
Drawing	

Downloaded from Arrow.com.

Belden Deutschland GmbH
Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.

Downloaded from Arrow.com.