


HONEYWELL
PART NUMBER

590-33AA33-503

REV	DOCUMENT	CHANGED BY	CHECK
E	0023729	CH 14AUG06	RK



CONNECTOR	AMP PART No. 104257-1
RECEPTACLES (2)	AMP PART No. 103358-4
LEADWIRES (2)	28 AWG, TEFLON INSULATED
HOUSING	ALUMINUM
THERM. CURVE, MAT'L	1, Q

ALL DIMS. NOM. UNLESS OTHERWISE NOTED.

RoHS Compliant

RESISTANCE (OHMS)

TEMP °C	MINIMUM	NOMINAL	MAXIMUM	REF	TOL
0	173,617	175,500	177,405	±0.2°C	
25	49,535	50,000	50,470	±0.2°C	
70	7,693.2	7,750	7,807.2	±0.2°C	

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±	-
ONE PLACE	.X	±	-
TWO PLACE	.XX	±	.01
THREE PLACE	.XXX	±	.005
FOUR PLACE	.XXXX	±	-
ANGLES	X	±	0°30'

THIRD ANGLE PROJECTION



DRAWN CH 14AUG06

CHECK RK 14AUG06

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

Honeywell

TITLE PROBE ASSEMBLY
OUTLINE

SIZE B	TYPE I	DRAWING NAME 590-33AA33-503	REV E
--------	--------	--------------------------------	----------

AUTOCAD	2D	SCALE NTS	SHEET	1 OF 1
---------	----	-----------	-------	--------