

5

4

3


2

1


Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802

No.1. contact


12,5 max.



nut thread



Printed board layout
component side



09 65 321 3701

M3

1

09 65 321 6701

M3

2

09 65 321 7701

M3

3

09 65 321 3702

4-40 UNC

1

09 65 321 6702

4-40 UNC

2

09 65 321 7702

4-40 UNC

3

Part number

Nut thread

Performance level

Mod.

Dat.

Name

Dat.

Name

Detail. 05/03/02

Insp.

Stand.



All Dim. in mm
Orig. Size DIN A 4

D-Sub, 25 poles,
male, straight,
with solder pins 3.7
and nuts.

Maßstab/
Scale

1.5:1

HARTING EURL
F-95972 Paris



TB 09 65 321 x70x

Sub.

Blatt/ Page

2