

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640066

Status:

Active

Overview:

Perma-Seal Terminals

Description:

Perma-Seal Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 1/4" (M6)

Documents:	
3D Model	Product Specification PS-19902-011-001 (PDF)
3D Model (PDF)	Product Specification PS-19902-013-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19164
Crimp Quality Equipment	Yes
Overview	Perma-Seal Terminals
Product Name	Perma-Seal
Type	Ring
UPC	800753113503
Physical	
Barrel Type	Closed
Insulation	NiAc
Material - Plating Mating	Tin
Net Weight	2.406/g
Packaging Type	Bag
Stud Size	1/4" (M6)
Wire Insulation Diameter	7.87mm
Wire Size AWG	10, 12
Wire Size mm²	3.09-5.01
Material Info	
Engineering Number	SC-230-14

Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19164-041



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19164 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Industrial Terminals, 10-22 AWG (see ATS)	640017400
Power Crimp Tool Head for Terminals 10-22 AWG Wire	640057400
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	640160041

This document was generated on 03/03/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION