



**Part Number :** [1301040026](#)  
**Product Description :** Haztex Hazardous Location  
26W with 12V Fluorescent Hand Lamp with In-line  
Transformer 16/3 SOOW Cord Type, Cord Length  
15.24m (50.0')  
**Series Number :** 130104  
**Status :** Active  
**Product Category :** Lamps and Lights  
**Engineering Number :** 1090-HZ12IB163



## Documents & Resources

## Product Environment Compliance

### Compliance

|                    |                                                  |
|--------------------|--------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                     |
| China RoHS         | Not Relevant                                     |
| EU ELV             | Not Relevant                                     |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21                  |
| REACH SVHC         | Not Reviewed per D(2024)7663-DC<br>(21 Jan 2025) |
| EU RoHS            | Not Reviewed per EU 2015/863                     |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

|                    |                                                                                                                                                          |
|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Status             | Active                                                                                                                                                   |
| Category           | Lamps and Lights                                                                                                                                         |
| Series             | 130104                                                                                                                                                   |
| Description        | Haztex Hazardous Location 26W with 12V Fluorescent Hand Lamp with In-line Transformer 16/3 SOOW Cord Type, Cord Length 15.24m (50.0')                    |
| Comments           | Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL) |
| NEMA Configuration | NEMA 5-15                                                                                                                                                |
| Product Name       | Haztex                                                                                                                                                   |
| Type               | Hand Lamps, Specialty Light                                                                                                                              |
| UPC                | 78678805478                                                                                                                                              |

### Agency

|    |        |
|----|--------|
| UL | E30252 |
|----|--------|

### Electrical

|                               |              |
|-------------------------------|--------------|
| Lamp Wattage - Maximum        | 26W          |
| Lumens                        | 1800         |
| On/Off Switch                 | No           |
| Voltage (Fixture) - Maximum   | 120VAC 60 HZ |
| Voltage (Secondary) - Maximum | 12V AC       |

### Physical

|                         |                |
|-------------------------|----------------|
| Bulb Type               | Fluorescent    |
| Cord Length - Primary   | 15.24m (50.0') |
| Cord Length - Secondary | N/A            |

|                     |                          |
|---------------------|--------------------------|
| Cord Type - Primary | 16/3 SOOW                |
| Depth               | 100.08mm (3.940")        |
| Duty                | Hazardous                |
| Guard Included      | Yes                      |
| Guard Type          | Cast Aluminum            |
| Height              | 482.60mm (19.000")       |
| Lamp Type           | PL-C 26/41/4P            |
| Length              | N/A                      |
| Material - Globe    | Tempered Soda-Lime Glass |
| Material - Guard    | Cast Aluminum            |
| Mounting Style      | Hand Held                |
| Net Weight          | 1258.000/kg              |
| Outlet              | None                     |
| Packaging Type      | Carton                   |

---

This document was generated on Sep 13, 2025