Part Number : 135170001
Product Description : Brick RFID Tag, 16.7m Read Range, 54.00 by 36.00mm Footprint, For Metal Surfaces, Screw or Rivet Attachment
Series Number : 13517
Status : Active
Product Category : Asset Tracking



Documents and Resources

Drawings

135170001_sd.pdf

Specifications

135170001-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Asset Tracking
Series	13517
Description	Brick RFID Tag, 16.7m Read Range, 54.00 by 36.00mm Footprint, For Metal Surfaces, Screw or Rivet Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Metal Surfaces
UPC	196823154157

Electrical

Frequency	902-928 MHz

Physical

Dimensions	54.00 x 36.00 x 12.50mm
Length	54.00mm
Mounting Style	Adhesive, Screws
Net Weight	9.400/g
Packaging Type	Bag
Read Range	16.8m
Thickness	12.50mm
Width	36.00mm

Downloaded from Arrow.com.