

USB 2.0 Adapter - USB-C to USB Micro-B (M/F)

MODEL NUMBER: **U040-000-MIC-F**



Connects your USB-C device to a USB-A host port using your existing USB Micro-B cable.

Description

The U040-000-MIC-F USB 2.0 Hi-Speed Adapter (M/F) allows you to connect an existing USB Micro-B cable between the USB-C port on your computer, laptop or tablet and a USB-A host port. This allows you to sync and charge your USB-C device without the extra expense of a new USB-C cable.

The portable, compact adapter supports USB 2.0 data transfer speeds up to 480 Mbps. The reversible USB-C male connector plugs into a USB-C port in either direction for fast, fumble-free connection every time.

Molded nickel-plated connectors with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. The U040-000-MIC-F is backward compatible with previous USB generations.

Features

Use Your Existing USB-C Device with an Existing USB Micro-B Cable

- Recommended for charging or synchronizing data on your USB-C computer, laptop or tablet
- Supports USB 2.0 data transfer speeds up to 480 Mbps
- Backward compatible with previous USB generations

Reversible USB-C Male Connector

- Fumble-free reversible plug connects in either direction to ensure fast, easy connection every time

Premium Construction

- Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss

Specifications

Highlights

- Supports data transfer speeds up to 480 Mbps
- Reversible USB-C plug provides fumble-free connection
- Gold-plated contacts for maximum conductivity and minimum data loss
- Backward compatible with previous USB generations

System Requirements

- USB-A host
- Device with USB-C female connector
- USB 2.0 Micro-B cable

Package Includes

- U040-000-MIC-F USB 2.0 Hi-Speed Adapter, USB-C to USB Micro-B (M/F)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332205032
Technology	USB 2.0 (High Speed); USB
INPUT	
Bus Powered	Yes
POWER	
USB Power Delivery (PD) Charging Support	No
PHYSICAL	
Color	Gray
Material of Construction	Aluminum
Shipping Dimensions (hwd / cm)	7.01 x 3.99 x 1.27
Shipping Dimensions (hwd / in.)	2.76 x 1.57 x 0.50
Shipping Weight (lbs.)	0.01
Unit Dimensions (hwd / in.)	0.24 x 0.4 x 0.98
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	5% to 95% RH, Non-Condensing
CONNECTIONS	
Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	MICRO-USB B (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	No
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Suspend Mode Support	No
Remote Wakeup Support	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>