



**Part Number :** [1062920805](#)

**Product Description :** MMC Male-to-(2) MPO Female Fiber Optic Breakout Patch Cord, Singlemode, 16 Fiber BIF Plenum Cable, 5.0m Length, Yellow Cable

**Series Number :** 86170

**Status :** Active

**Product Category :** Fiber Optic Cable Assemblies



---

## Documents and Resources

### Drawings

[1062920805\\_sd.pdf](#)

### Specifications

[1062920301-000.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	86170
Description	MMC Male-to-(2) MPO Female Fiber Optic Breakout Patch Cord, Singlemode, 16 Fiber BIF Plenum Cable, 5.0m Length, Yellow Cable
Connector to Connector	MMC-to-(2) MPO
Mode	Singlemode
Product Name	MMC,MPO
UPC	198282432838

### Physical

Boot Type	Straight
Cable Length	5.0m
Cable Size	2.50mm, 3.00mm
Fiber (Core/Cladding)	9/125µm
Net Weight	1.000/g
Single Ended	No
Wire/Cable Type	16 Fiber Bend-insensitive Plenum