





- Protection level: IP67
- Temperature range: -25°C ... +80°C

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

4.0 to 100	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

Part no.	213496974XXXXX
----------	----------------

Type of cable	XX
PVC grey, 4x1.5mm ²	XX=95
PUR black, 4x1.5mm ²	XX=96

All rights reserved
Department EC PD - RO
HARTING Electronics GmbH
D-32339 Espelkamp

All Dimensions in mm
Original Size DIN A3

Scale
1.5:1

Free size tol.

Created by
TAMAS

Inspected by
AVRAM

Standardisation
HOFFMANN

Date
2014-07-01

State
Final Release

Title
7/8 Cable Assembly

Type
TB

Number
213496974XXXXX

Doc-Key / ECM-Nr.
100581015/UGD/009/A
500000076597

Rev.
A

Page
1/1