

## Specification Sheet

Part Number: 161-64008



Helawrap, Accessory Clip, HWCLIP25, 1" Dia, PA66HIRHS, Black, 50/pkg

<b>Article Number</b>	161-64008
-----------------------	-----------

<b>Type</b>	HWCLIP25
-------------	----------

<b>Color</b>	Black (BK)
--------------	------------

<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• An innovative coupling system allows for an unlimited number of bundling combinations.</li><li>• Clips can be easily released and reused.</li><li>• Clips swivel freely which reduces mechanical stress and eliminates pinch points.</li><li>• High Impact Polyamide 6.6 material provides firm fit even in rugged conditions.</li><li>• Consists of acrylate adhesive with base of polyurethane foam allowing it to adhere firmly and easily to nearly any surface.</li></ul>
--------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

<b>Quantity Per</b>	bag
---------------------	-----

<b>Product Description</b>	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Clips can be joined to a base and another clip of any size. Different cable sizes can be bundled together, organized and protected flexibly and efficiently.
<b>Short Description</b>	Helawrap, Accessory Clip, HWCLIP25, 1" Dia, PA66HIRHS, Black, 50/pkg
<b>Global Part Name</b>	HWCLIP25-PA66HIRHS-BK
<b>Fixation Method</b>	Plug-in mounting
<b>Diameter D (Imperial)</b>	0.98
<b>Diameter D (Metric)</b>	25
<b>Nominal Diameter (Imperial)</b>	1
<b>Nominal Diameter (Metric)</b>	25.0
<b>Material</b>	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
<b>Material Shortcut</b>	PA66HIRHS
<b>Flammability</b>	UL 94 HB
<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)

<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	50
<b>Package Quantity (Metric)</b>	50
<b>Customs Number</b>	3926909988
<b>Weight (Metric)</b>	0.19
<b>Weight (Imperial)</b>	0.42

© 2020 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)