



Part Number : [1300990163](#)

Product Description : MAX-LOC/Watertite Strain Relief Cord-Sealing Grip, 3/4" NPT, 90° Angle Male, Cable Diameter 9.53-11.10mm (.375-.437") Non-Metallic Mesh

Series Number : 130099

Status : Active

Product Category : Cable Grips

Engineering Number : 5625NM



Documents & Resources

Drawings

[1300990163_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	Cable Grips
Series	130099
Description	MAX-LOC/Watertite Strain Relief Cord-Sealing Grip, 3/4" NPT, 90° Angle Male, Cable Diameter 9.53-11.10mm (.375-.437") Non-Metallic Mesh
NEMA Rating	NEMA 3R
Product Name	MAX-LOC,Watertite
Type	Strain Relief Grip
UPC	78678856255

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	9.53-11.10mm (.375-.437")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	Nylon
Mesh Length	N/A
Number of Holes	1
O-Ring	No
Thread Size	3/4" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	<u>1300990144</u>
MAX-LOC Gasket Sealing Ring, 3/4" NPT, Black	<u>1300990150</u>
MAX-LOC O-Ring, 3/4" NPT	<u>1301800333</u>

This document was generated on Sep 13, 2025