
EB 3-20/PT - Insertion bridge

3260068

https://www.phoenixcontact.com/ae/products/3260068

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 20 mm, number of positions: 3, length: 65 mm, color: red



Commercial data

Item number	3260068
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE2
Product key	BE2Z2X
GTIN	4046356997997
Weight per piece (including packing)	42.79 g
Weight per piece (excluding packing)	42.79 g
Customs tariff number	85366990
Country of origin	PL

Downloaded from Arrow.com.

Technical data

Product properties

Product type	Insertion bridge
Number of positions	3
Pitch	20 mm

Electrical properties

Maximum load current	150 A

Connection data

Maximum load current	150 A

Dimensions

Width	55.3 mm
Height	64.5 mm
Depth	27.9 mm
Length	64.5 mm
Pitch	20 mm

Material specifications

Color	red (RAL 3001)
Material	Metal
Flammability rating according to UL 94	V0
Coating	tin-plated
Insulating material	PA

Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 9.0	EC000489

UNSPSC

UNSPSC 21.0	39121400

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Middle East FZ LLC
1201N-1206N, Dubai Science Park Towers – North
P.O. Box 345002, Dubai, United Arab Emirates
(+971) 4 437-0324
info-me@phoenixcontact.com

Downloaded from Arrow.com.