The protection you rely on.

Our Bussmann series products reflect a longstanding tradition of leading fusible circuit protection and electrical safety solutions that protect equipment and enable reliable, efficient power distribution.

With Eaton you get the industry's top innovator in fuse technology and unmatched expertise in circuit breakers. Our heritage in circuit breaker development coupled with the number one name in fuses means the choice is no longer fuse or breaker. It's fuse and breaker— it's leadership in circuit protection.



BUSSMANN SERIES



British Standard (BS) Fuse Links and Fuse Holders

Fuse links for general industrial applications with Q1 fusing factor, general purpose (gG) and motor protection (gM) characteristics for general industrial and motor applications.

Standard:	BS88 part 1 to 6, IEC 60269 part 1 and 2
Rated voltage:	415, 550 and 690Vac
Rated current:	2 to 1250A
Breaking capacity:	80kA
Operating class:	gG and gM
Sizes:	A1 to A4, B1 to B4, C1 to C3, D2, E1, F1 and F2 and non standard sizes
Fuse holders:	Full range of fuse holders available (Red Spot, Camaster and Safeloc)
Applications:	Residential, commercial and industrial

Bussmann series BS88 industrial fuse links



NSD32

Item no.	Bussmann/GE Item no.	Amps	Fuse holder	Volts	Dim	Box qty
Clip in type.						
NSD2	**NS2**	2	32NNS* SC32*	550	58.5mm	20
NSD4	**NS4**	4				
NSD6	**NS6**	6				
NSD10	**NS10**	10				
NSD16	**NS16**	16				
NSD20	**NS20**	20				
NSD25	**NS25**	25				
NSD32	**NS32**	32				
NSD20M25	**NS20M25**	20M25	32NNS* SC32*	415	58.5mm	20
NSD20M32	**NS20M32**	20M32				
NSD32M36	**NS32M36**	32M36				
NSD32M40	**NS32M40**	32M40				
NSD32M50	**NS32M50**	32M50				
NSD32M63	**NS32M63**	32M63				

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links

Item no.	Bussmann/GE Item no.	Amps	Fuse holder	Volts	Dim	Box qty
SSD2	**SS2**	2				
SSD4	**SS4**	4				
SSD6	**SS6**	6				
SSD10	**SS10**	10		240	47.0mm	20
SSD16	**SS16**	16				
SSD20	**SS20**	20				
SSD25	**SS25**	25				
SSD32	**SS32**	32				


SSD32

ESD2		2				
ESD4		4				
ESD6		6				
ESD10		10				
ESD16		16				
ESD20		20	63ENS* SC63*	550	68.0mm	20
ESD25		25				
ESD32		32				
ESD40	**ES40**	40				
ESD50	**ES50**	50				
ESD63	**ES63**	63				
ESD63M80	**ES63M80**	63M80	63ENS* SC63*	415	68.0mm	20
ESD63M100		63M100				


ESD63

Offset bolted tags						
STD2	**LST2**	2				
STD4	**LST4**	4				
STD6	**LST6**	6				
STD10	**LST10**	10		240	35.0mm	20
STD16	**LST16**	16				
STD20	**LST20**	20				
STD25	**LST25**	25				
STD32	**LST32**	32				


STD10

NITD2	**NIT2L**	2				
NITD4	**NIT4L**	4				
NITD6	**NIT6L**	6				
NITD10	**NIT10L**	10	CM32FC RS20*	550	44.5mm	20
NITD16	**NIT16L**	16				
NITD20	**NIT20L**	20				
NITD25	**NIT25L**	25				
NITD32	**NIT32L**	32				
NITD20M25	**NIT20M25L**	20M25				
NITD20M32	**NIT20M32L**	25M32				
NITD32M40	**NIT32M40L**	32M40	CM32FC RS32*	415	44.5mm	20
NITD32M50	**NIT32M50L**	32M50				
NITD32M63	**NIT32M63L**	32M63				


NITD6

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links



AAO32



BAO63



OSD100



DEO200



AC32

Item no.	Bussmann/GE Item no.	Amps	Fuse holder	Volts	Dim	Box qty
Offset bolted tags						
AAO2	**TIA2L**	2	CM32F RS32 RS63	550	73.5mm	20
AAO4	**TIA4L**	4				
AAO6	**TIA6L**	6				
AAO10	**TIA10L**	10				
AAO16	**TIA16L**	16				
AAO20	**TIA20L**	20				
AAO25	**TIA25L**	25				
AAO32	**TIA32L**	32				
AAO32M40	**TIA32M40L**	32M40				
AAO32M50	**TIA32M50L**	32M50				
AAO32M63	**TIA32M63L**	32M63				
BAO35	**TIS35L**	35	CM63F RS63	550	73.5mm	20
BAO40	**TIS40L**	40				
BAO50	**TIS50L**	50				
BAO63	**TIS63L**	63				
BAO63M80	**TIS63M80L**	63M80				
BAO63M100	**TIS63M100L**	63M100				
OSD80	**OS80**	80	CM100F	415	73.0mm	20
OSD100	**OS100**	100				
OSD100M125	**OS100M125**	100M125				
OSD100M160		100M160				
CEO32		32	RS100*	550	94.0mm	10
CEO40		40				
CEO50		50				
CEO63		63				
CEO80	**TCP80L**	80				
CEO100	**TCP100L**	100				
CEO100M125	**TCP100M125L**	100M125	RS100*	415	94.0mm	10
CEO100M160	**TCP100M160L**	100M160				
CEO100M200	**TCP100M200L**	100M200				
DEO125	**TFP125L**	125		415	94.0mm	5
DEO160	**TFP160L**	160				
DEO200	**TFP200L**	200				
DEO200M250	**TFP200M250L**	200M250				
DEO200M315	**TFP200M315L**	200M315				
Centre bolted tags - 2 hole fixing.						
AC2		2		550	97.5mm	20
AC4		4				
AC6		6				
AC10		10				
AC16		16				
AC20		20				
AC25		25				
AC32		32				
BC40		40				
BC50		50				
BC63		63				
BC63M80		63M80				
BC63M100		63M100				

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links

Item no.	Bussmann/GE Item no.	Amps	Fuse holder	Volts	Dim	Box qty
Centre bolted tags - 2 hole fixing.						
AD2		2	RS200*	550	111.5mm	20
AD4		4				
AD6		6				
AD10		10				
AD16		16				
AD20		20				
AD25		25				
AD32		32				
BD40		40				
BD50		50				
BD63		63				
CD80	**TC80L**	80	RS200*	550	111.0mm	10
CD100	**TC100L**	100				
CD100M125		100M125	RS200*	415	111.0mm	10
CD100M160		100M160				
CD100M200		100M200				
DD125	**TF125L**	125	RS200*	415	111.0mm	5
DD160	**TF160L**	160				
DD200	**TF200L**	200				
DD200M250	**TF200M250L**	200M250				
DD200M315	**TF200M315L**	200M315				
ED250	**TKF250L**	250		415	111mm	1
ED315	**TKF315L**	315				
ED355	**TMF355L**	355				
ED400	**TMF400L**	400				
ED315M400	**TKF315M400L**	315M400				
ED400M500		400M500		550	111mm	1
EFS125		125	RS400*	415	133mm	1
EFS160		160				
EFS200		200				
EFS250	**TKM250L**	250				
Centre bolted tags - 4 hole fixing.						
EFS315	**TKM315L**	315		415	133/ 184mm	1
EF355	**TM355L**	355		415	133/ 184mm	1
EF400	**TM400L**	400				
EF400M500		400M500		550		
FF450	**TTM450L**	450		550	133/ 184mm	1
FF500	**TTM500L**	500				
FF560	**TTM560L**	560				
FF630	**TTM630L**	630				
FG450		450		550	133/ 184mm	1
FG500		500				
FG560		560				
FG630		630				


AD32


DD200


ED315


EFS315


FF630

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links



GG710



200N20



NITD6



H07-660

Item no.	Bussmann/GE Item no.	Amps	Fuse holder	Volts	Dim	Box qty
Centre bolted tags - 4 hole fixing.						
GF710	**TLM710L**	710		550	133/ 184mm	1
GF800	**TLM800L**	800				
GG710		710		550	167/ 231mm	1
GG800		800				
GG1000		1000				
GG1250		1250				
GH710		710		550	149mm	1
GH800		800				
GH1000		1000				
GH1250		1250				
Special tag arrangements - 660Vac / 400Vdc.						
125N20		125		660	92.5mm	1
160N20		160				
200N20		200				
250N20		250				
315N20		315				
355P20		355				
400P20		400				
450R20		450				
500R20		500				
560R20		560				
630R20		630				
710S20		710		550	92.5mm	1
800S20		800				
Offset bolted tags						
	NIT2	2	CM32FC RS20*	550	44.5mm	20
	NIT4	4				
	NIT6	6				
	NIT10	10				
	NIT16	16				
	NIT20	20				
	NET25	25	CM32FC RS32*	440	44.5mm	20
	NET32	32				
	NIT20M25	20M25	CM32FC RS32*	415	44.5mm	20
	NIT20M32	25M32				
	NIT32M40	32M40				
	NIT32M50	32M50				
	NIT32M63	32M63				
Offset bolted tags - 660V.						
2H07-660	**TIA2**	2	CM63F RS63*	660	73.5mm	20
4H07-660	**TIA4**	4				
6H07-660	**TIA6**	6				
10H07-660	**TIA10**	10				
16H07-660	**TIA16**	16				
20H07-660	**TIA20**	20				
25H07-660	**TIA25**	25				
32H07-660	**TIA32**	32				
	TIA32M35	32M35				
	TIA32M40	32M40				
	TIA32M50	32M50				
	TIA32M63	32M63				

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links

Item no.	Bussmann/GE Item no.	Amps	Fuse holder	Volts	Dim	Box qty
Offset bolted tags - 660V.						
	TIS35	35	CM63F RS63*	660	73.5mm	20
40K07-660	**TIS40**	40				
50K07-660	**TIS50**	50				
63K07-660	**TIS63**	63				
	TIS63M80	63M80				
	TIS63M100	63M100				
80L14-660	**TCP80**	80	RS100*	660	94mm	20
100L14-660	**TCP100**	100				
	TCP100M125	100M125				
	TCP100M160	100M160				
	TCP100M200	100M200				
125M14-660	**TFP125**	125		550	94mm	10
160M14-660	**TFP160**	160				
200M14-660	**TFP200**	200				
Centre bolted tags - 660V.						
2K08-660	**TB2**	2		660	97.5mm	1
4K08-660	**TB4**	4				
6K08-660	**TB6**	6				
10K08-660	**TB10**	10				
16K08-660	**TB16**	16				
20K08-660	**TB20**	20				
25K08-660	**TB25**	25				
32K08-660	**TB32**	32				
40K08-660	**TB40**	40				
50K08-660	**TB50**	50				
63K08-660	**TB63**	63				
2K09-660	**TBC2**	2	RS200*	660	111mm	1
4K09-660	**TBC4**	4				
6K09-660	**TBC6**	6				
10K09-660	**TBC10**	10				
16K09-660	**TBC16**	16				
20K09-660	**TBC20**	20				
25K09-660	**TBC25**	25				
32K09-660	**TBC32**	32				
40K09-660	**TBC40**	40				
50K09-660	**TBC50**	50				
63K09-660	**TBC63**	63				
	TBC63M100	63M100				
80L09-660	**TC80**	80	RS200*	660	111mm	20
100L09-660	**TC100**	100				
125M09-660	**TF125**	125		660	111mm	20
160M09-660	**TF160**	160				
200M09-660	**TF200**	200				
	TF200M250	200M250				
	TF200M315	200M315				
250N09-660	**TKF250**	250		660	111mm	1
315N09-660	**TKF315**	315				
	TKF315M355	315M355				



K07-660


L14-660


K08-660


L09-660


M09-660

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links and fuse holders

Item no.	Bussmann/GE Item no.	Amps	Fuse holder	Volts	Dim	Box qty
Centre bolted tags - 660V.						
355P09-660	**TMF355**	355		660	111mm	1
400P09-660	**TMF400**	400				
125N11-660		125		660	133mm	1
160N11-660		160				
200N11-660		200				
250N11-660	**TKM250**	250				
315N11-660	**TKM315**	315				
355P11-660	**TM355**	355		660	184 / 133mm	1
400P11-660	**TM400**	400				
450R11-660	**TTM450**	450		550	184 / 133mm	1
500R11-660	**TTM500**	500				
560R11-660	**TTM560**	560				
630R11-660	**TTM630**	630				
450R12-660	**TT450**	450		550	231 / 167mm	1
500R12-660	**TT500**	500				
560R12-660	**TT560**	560				
630R12-660	**TT630**	630				
	TLM670	670		660	184 / 133mm	1
	TLM710	710				
	TLM750	750				
	TLM800	800				



SAFEloc

Item no.	Description	Amps	Fuse holder	Volts	Dim	Box qty
SAFEloc fuse holders						
32NNSF	Front wired		NS / NSD	32	690	10
32NNSR	Back wired					
32NNSBS	Back stud					
32NNSFBS	Front wired / back stud					
32NNSFWHITE	Front wired, white					
32NNSFBSWHITE	F. Wired / b. Stud, white					
32NNSBSWHITE	Back stud, white					
63ENSF	Front wired		ES / ESD	63	690	10
63ENSR	Back wired					
63ENSBS	Back stud					
63ENSFBS	Front wired / back stud					
63ENSFWHITE	Front wired, white					
63ENSFBSWHITE	Front wired / back stud, white					
63ENSBSWHITE	Back stud, white					
32NNL	Neutral link		32NNS*		690	10
63ENL	Neutral link		63ENS*			

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links and fuse holders

Item no.	Description	Amps	Fuse holder	Volts	Dim	Box qty
CAMaster fuse holders						
CM32FC	Front wired		NITD	32	690	10
CM32F	Front wired		AAO	32		
CM63F	Front wired		BAO	63		5
CM100F	Front wired		OSD	100		
CM32FCW	Front wired, white		NITD	32	690	10
CM32FW	Front wired, white		AAO	32		
CM63FW	Front wired, white		BAO	63		5
CM100FW	Front wired, white		OSD	100		



CAMaster

Item no.	Description	Fuse holder to suit.	Volts	Box qty
CAMaster accessories.				
32CMLC	Bolted neutral link	CM32FC	690	10
32CML	Bolted neutral link	CM32F		1
63-100CML	Bolted neutral link	CM63F & CM100F		1
32BS	Back stud conversion kits	CM32FC & CM32F	690	10
63/100BS	Back stud conversion kits	CM63F & CM100F		5
32LSCC	Lockable safety carrier	CM32FC	690	3
32LSC	Lockable safety carrier	CM32F		3
63-100LSC	Lockable safety carrier	CM63F & CM100F		3



CAMaster accessories - Studs

Item no.	Description	Fuse	Amps	Volts	Box qty
Safeclip fuse holders					
SC20H	Front wired	NS / NSD	20	415	10
SC20P	Back stud				
SC20BH	Busbar connect / front connect				
SC20HWH	Front wired, white				
SC32H-D	Front wired	NS / NSD	32	415	10
SC32PH-D	Front wired / back stud				
SC32BH	Busbar connect / front connect				
SC32P	Back stud				
SC32H-DWH	Front wired, white				
SC32PWH	Back stud, white				
SC32PH-DWH	Front wired / back stud - white				
SC63H-D	Front wired	ES / ESD	63	415	10
SC63BH	Busbar connect / front connect				
SC63P	Back stud				
SC63H-DWH	Back stud, white				



Safeclip fuseholder - black



Safeclip fuseholder - white

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links and fuse holders



Red spot fuseholder - black



Red spot fuseholder - white



RS63LOCK

Item no.	Description	Fuse	Amps	Volts	Box qty
Red spot fuse holders					
RS20H	Front wired	NIT / NITD	20	690	10
RS20BW	Back wired				
RS20P-G	Back stud				
RS20PH-G	Front wired / back stud				
RS20H-WH	Front wired, white				
RS20PG-WH	Back stud, white				
RS32H	Front wired	TIA / AAO	32	690	10
RS32BW	Back wired				
RS32P	Back stud				
RS32PH	Front wired / back stud				
RS32HWH	Front wired, white				
RS32PWH	Back stud, white				
RS63H	Front wired	TIA / TIS AAO / BAO	63	690	5
RS63BW	Back wired				
RS63P	Back stud				
RS63PH	Front wired / back stud				
RS63HWH	Front wired, white				
RS63PWH	Back stud, white				
RS100H	Front wired	TCP / CEO	100	690	5
RS100BW	Back wired				
RS100P	Back stud				
RS100PH	Front wired / back stud				
RS100HWH	Front wired, white				
RS100PWH	Back stud, white				
RS200H	Front wired	TC / TF CD / DD	200	690	1
RS200P	Back stud				
RS200PH	Front wired / back stud				
RS200HWH	Front wired, white				
RS200PWH	Back stud, white				
RS400H	Front wired	TKM / TM EFS / EF	400	690	1
RS400P	Back stud				
RS400PH	Front wired / back stud				
Redspot accessories.					
RS20LOCK	Pad lockable inserts		20	690	3
RS32LOCK	Pad lockable inserts		32		
RS63LOCK	Pad lockable inserts		63		
RS100LOCK	Pad lockable inserts		100		
RS20RED	Red isolation carriers		20	690	5
RS32RED	Red isolation carriers		32		
RS63RED	Red isolation carriers		63		
RS100RED	Red isolation carriers		100		
P110151-10	RS20CLINK	Bolted Neutral Links	20	690	5
P110152-10	RS32CLINK		32		
P110153-10	RS63CLINK		63		
P110154-10	RS100CLINK		100		

Downloaded from Arrow.com.

LV Fuse gear

Type J Feeder Pillar Fuse Links

Cylindrical type fuse links designed to be used with wedge type fuse carriers on BS applications. These fuse links will be used by Electrical Authorities in distribution pillars, open type substation boards, heavy duty cut-outs and underground connection boxes. Can also be fitted in pole or wall mounted outdoor service fuse links.



Standard:	BS88 Part 5
Rated voltage:	415Vac
Rated current:	20 to 800A
Breaking capacity:	80kA
Operating class:	gG
Sizes:	76, 82 and 92mm centres
Fuse holders:	Designed to be used with wedge type fuse carriers
Applications:	Utilities (Available in cylindrical slotted or non slotted tag versions)

Bussmann series BS88 'J' type industrial fuse links

Item no.	Amps	Fuse holder	Volts	Dim	Box qty
20MJ25-6	20				
32MJ25-6	32				
40MJ25-6	40				
63MJ25-6	63				
80MJ25-6	80		415	46 x 39 mm	5
100MJ25-6	100				
125MJ25-6	125				
160MJ25-6	160				
200MJ25-6	200				
250MJ25-6	250				
63MJ26-6	63				
80MJ26-6	80				
100MJ26-6	100				
125MJ26-6	125		415	76mm	5
160MJ26-6	160				
200MJ26-6	200				
250MJ26-6	250				
20MJ30-8	20				
32MJ30-8	32				
40MJ30-8	40				
50MJ30-8	50		415	82mm	5
63MJ30-8	63				
80MJ30-7	80				
100MJ30-7	100				
125MJ30-7	125				
160MJ30-7	160				
200MJ30-7	200				
250MJ30-7	250		415	82mm	5
315MJ30-7	315				
355PJ30-7	355				
400PJ30-7	400				
20MJ31-8	20				
25MJ31-8	25				
32MJ31-8	32				
40MJ31-8	40				
50MJ31-8	50				
63MJ31-8	63				
80MJ31-7	80				
100MJ31-7	100		415	92mm	5
125MJ31-7	125				
160MJ31-7	160				
200MJ31-7	200				
250MJ31-7	250				
315MJ31-7	315				
355PJ31-7	355				
400PJ31-7	400				



MJ30-8



MJ31-7

Downloaded from Arrow.com.

LV Fuse gear



House Service Cut-Out Fuse Links and Fuse Holders

Cylindrical fuse links to be used in connection with house service cut-out for utility/residential applications. Modular fuse holders to be used with our KR85 and LR85 range.

Standard:	ASTA Certified and tested in accordance to BS1361 and AS2005
Rated voltage:	415Vac
Rated current:	20 to 100A
Breaking capacity:	33kA
Operating class:	gG
Sizes:	22.2 and 30.2mm
Fuse holders:	60/80SP for KR Series or 100SP for LR Series
Applications:	Protection of incoming cables into residential and commercial properties

Bussmann series BS88 industrial fuse links and fuse holders



House service fuse holder clear



House service fuse holder black

Item no.	Description	Amps	Fuse	Volts	Box qty
House service fuse holders.					
HSB30BWI	Back wire, black	100	LR85	415	10
HSB30FWI	Front wire, black				
HSB30BWCLI	Back wire, clear				
HSB30FWCLI	Front wire, clear				
HSB22BW	Back wire, black	100	KR85	415	10
HSB22FW	Front wire, black				
HSB22BWCL	Back wire, clear				
HSB22FWCL	Front wire, clear				
HSB22BWCL-Q*	Back wire, clear	125		415	10
HSB22FWCL-Q*	Front wire, clear				
Complete with link and fixing screws - Queensland only					
HSB22BW-V	Back wired	100	KR85	415	10
Complete with two-hole fixing - Victoria only					



100KR85



80LR85

Item no.	Amps	Fuse holder	Volts	Dim	Box qty
House service fuse links.					
5KR85	5	HSB22*	415	22 X 57 mm	20
10KR85	10				
15KR85	15				
20KR85	20				
25KR85	25				
30KR85	30				
40KR85	40				
45KR85	45				
50KR85	50				
60KR85	60				
80KR85	80				
100KR85	100				
30LR85	30	HSB30*	415	30 X 57 mm	20
40LR85	40				
50LR85	50				
60LR85	60				
80LR85	80				
100LR85	100				

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links

Item no.	Amps	Fuse holder	Volts	Dim	Box qty
Consumer fuse links.					
C180-1A	1		250	6.3 x 25 mm	10
C180-2A	2				
C180-3A	3				
C180-5A	5				
C180-7A	7				
C180-10A	10				
C180-13A	13				
SMD2	2		415	12.7 x 29 mm	10
SMD4	4				
SMD6	6				
SMD8	8				
SMD10	10				
SMD16	16				
SMD20	20				
SMD25	25				
SMD32	32				
C55	5		415	6.3 x 25mm	20
C1515	15		415	10.3 x 26mm	
C1520	20		415		
C3030	30		415	12.7 x 29mm	
C4545	45		415	16.7 x 35mm	



C180-5A



C1520

Item no.	Description	Amps	Volts	Dim	Box qty
Joint service / nato fuse links					
059-0107	Ferrule	0.25	440	6.3 x 32mm	25
059-0108	Ferrule	0.5			
059-0109	Ferrule	1			
059-0110	Ferrule	2			
059-0111	Ferrule	3			
059-0112	Ferrule	5			
059-0113	Ferrule	7			
011-9925	Ferrule	10			
011-9926	Ferrule	15			
059-0140	Ferrule	0.5	440	12 x 33.6 mm	25
059-0141	Ferrule	1			
059-0142	Ferrule	2			
059-0143	Ferrule	3			
059-0144	Ferrule	5			
059-0145	Ferrule	7			
059-0146	Ferrule	10			
059-0147	Ferrule	15			
011-9483	Ferrule	20			



059-0144

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series BS88 industrial fuse links



059-0114



059-0148



059-0123

Item no.	Description	Amps	Fuse holder	Volts	Dim	Box qty
Joint service / nato fuse links						
059-0114	Offset bolted tag	0.5		440	Tag 45mm Fix Ctr	25
059-0115	Offset bolted tag	1				
059-0116	Offset bolted tag	2				
059-0117	Offset bolted tag	3				
059-0118	Offset bolted tag	5				
059-0119	Offset bolted tag	7				
059-0120	Offset bolted tag	10				
059-0121	Offset bolted tag	15				
011-9679	Offset bolted tag	20				
012-0140	Offset bolted tag	30				
059-0148	Ferrule	10		440	16.7 X 38 mm	25
059-0149	Ferrule	15				
059-0150	Ferrule	20				
059-0151	Ferrule	30				
059-0122	Offset bolted tag	10		440	Tag 56mm Fix Ctr	25
059-0123	Offset bolted tag	15				
059-0124	Offset bolted tag	20				
059-0125	Offset bolted tag	30				
012-0067	Offset bolted tag	40				
011-9127	Offset bolted tag	50				
012-0141	Offset bolted tag	60				

Bussmann series mining & traction fuses & fuse holders - 1200V


HD36

Item no.	Description	Amps	Fuse holder	Volts	Dim	Box qty
Mining / traction fuse links - 1200V.						
1HD36		1		1200 Vac 750 Vdc	122 mm	10
2HD36	TAC2	2				
4HD36	TAC4	4				
6HD36	TAC6	6				
10HD36	TAC10	10				
15HD36	TAC16	15				
20HD36	TAC20	20				
25HD36	TAC25	25				
30HD36	TAC32	30				
35KC36	TSC35	35		1200 Vac 750 Vdc	122 mm	10
40KC36		40				
50KC36	TSC50	50				
60KC36	TSC63	60				
NBC-80	TFC80	80		1200 Vac 1000 Vdc	168 mm	1
NBC-100	TFC100	100				
NBC-125	TFC125	125				
NBC-150	TFC150	150				
NBC-200	TFC200	200				


RSL63H

RSL63H	Front wired	63		1200 Vac 750 Vdc	122 mm	1
RSL63P	F-wired / b-stud					
RSL63PH	Back stud					

Downloaded from Arrow.com.

LV Fuse gear

IEC Cylindrical Fuse Links and Fuse Holders

Cylindrical fuse links for industrial applications, class gG. Available with indicator or striker.
Cylindrical fuse links for industrial applications, class aM (Motor protection). Available with indicator.
Modular fuse holders specifically designed for the protection of general industrial and commercial applications such as power distribution, lighting, cable and motor protection.

Standard:	IEC 60269
Rated voltage:	400, 500 and 690Vac
Rated current:	0.5 to 125A
Breaking capacity:	20 to 120kA
Operating class:	gG and gM
Sizes:	8x31, 10x38, 14x51 and 22x58mm
Fuse holders:	Full range of fuse holders available (CH Series)
Applications:	Industrial and commercial



Bussmann series DIN industrial fuses & fuse holders

Item no.	Amps	Type	Fuse holder	Volts	Dim	Box qty
Cylindrical fuses.						
C08G (A)	2, 4, 6, 10, 16, 20, 25, 32	gG		400	8.5 X 31mm	10
C08M(A)	2, 4, 6, 10, 16, 20, 25, 33	aM				
C10G (A)	0.5, 1, 2, 4, 6, 8, 10, 16, 20, 25, 32	gG	CHM1DU	500	10 X 38mm	10
C10M(A)	0.5, 1, 2, 4, 6, 8, 10, 16, 20, 25, 33	aM				
C14G (A)	0.5, 1, 2, 4, 6, 8, 10, 16, 20, 25, 32, 40, 50	gG	CH141B	690	14 X 51mm	10
C14GM(A)	0.5, 1, 2, 4, 6, 8, 10, 16, 20, 25, 32, 40, 51	aM				
C22G (A)	0.5, 1, 2, 4, 6, 8, 10, 16, 20, 25, 32, 40, 50, 63, 80, 100	gG	CH221B	690	22 X 51mm	10
C22M(A)	0.5, 1, 2, 4, 6, 8, 10, 16, 20, 25, 32, 40, 50, 63, 80, 100	aM				



C08G



C10G



C14G



C22M

Item no.	Amps	Fuse size	Volts	Box qty
Cylindrical fuse holders.				
CHM1DU	32	10 x 38mm	690	12
CH141B	50	14 x 51mm	690	8
CH221B	125	22 x 58mm	690	6
CHCC1DU	32	10 x 38mm Rejection	690	12
AL-D	Multi pole fuseholder connectors - 10 x 38		Pack	12



CHM1DU

Item no.	Suits fuse links	Amps	Volts	Poles	Box qty
CCP - compact circuit protector.					
CCP-1-30CC	LP-CC, KTK-R, FNQ-R	30	600 Vac	1	12
CCP-3-30CC				3	
CCP-1-30M	KTK, FNQ			1	8
CCP-3-30M	C10G, C10M			3	
CCP-1-DCM	PVM		80Vdc	1	
CCP-PLC-IND	Remote fuse indicator				
CCP-AUX	Auxillarm contact				
DIN industrial fuse links - 500V - gG.					



CCP - compact circuit protector

Downloaded from Arrow.com.

LV Fuse gear



NH DIN Industrial Fuse Links & Bases

A square bodied range of industrial fuse links for a wide variety of applications.
NH fuse bases with thermoplastic bodies, DIN rail and/or screw mounting (size 4 screw mounting only).
Range of accessories including phase barriers, IP20 finger-safe protection kits and neutral links available.

Standard:	IEC 60269 and VDE 0636
Rated voltage:	400, 500 and 690Vac
Rated current:	2 to 1250A
Breaking capacity:	120kA
Operating class:	gG and aM
Sizes:	000 to 4 (size 4 bolted only version)
Fuse holders:	Available for all fuse links sizes
Applications:	Industrial & commercial (Available with Dual Indication and Insulated Metal Gripping Lugs)

Bussmann series DIN industrial fuses & fuse holders



NHG000B

Item no.	Type		Fuse holder	Amps	Volts	Size	Box qty
10NHG000B	gG/gL (Standard)		SD00-D TD00-D	10	500	000	3
16NHG000B				16			
20NHG000B				20			
25NHG000B				25			
32NHG000B				32			
40NHG000B				40			
50NHG000B				50			
63NHG000B				63			
80NHG000B				80			
100NHG000B				100			
125NHG00B	gG/gL (Standard)		SD00-D TD00-D	125	500	00	3
160NHG00B				160			



NHG01B

10NHG01B	gG/gL (Standard)		SD1-D TD1-D	10	500	1	3
16NHG01B				16			
20NHG01B				20			
25NHG01B				25			
32NHG01B				32			
40NHG01B				40			
50NHG01B				50			
63NHG01B				63			
80NHG01B				80			
100NHG01B				100			
125NHG01B				125			
160NHG01B				160			
200NHG1B				200			
224NHG1B				224			
250NHG1B				250			



NHG02B

50NHG02B	gG/gL (Standard)		SD2-D TD2-D	50	500	2	3
63NHG02B				63			
80NHG02B				80			
100NHG02B				100			
125NHG02B				125			
160NHG02B				160			
200NHG02B				200			
224NHG02B				224			
250NHG02B				250			
315NHG2B				315			
355NHG2B				355			
400NHG2B				400			
DIN industrial fuse links - 500V - gG.							

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series DIN industrial fuses & fuse holders

Item no.	Type	Fuse holder	Amps	Volts	Size	Box qty
250NHG03B	gG/gL (Standard)	SD3-D TD3-D	250	500	3	3
315NHG03B			315			
355NHG03B			355			
400NHG03B			400			
500NHG3B			500			
630NHG3B			630			



NHG03B

DIN industrial fuse links - 690V - gG.						
10NHG000B-690	gG/gL (Standard)	SD00-D TD00-D	10	690	000	3
16NHG000B-690			16			
20NHG000B-690			20			
25NHG000B-690			25			
32NHG000B-690			32			
40NHG000B-690			40			
50NHG00B-690			50			
63NHG00B-690	gG/gL (Standard)	SD00-D TD00-D	63	690	00	3
80NHG00B-690			80			
100NHG00B-690			100			



NHG000B-690

50NHG1B-690	gG/gL (Standard)	SD1-D TD1-D	50	690	1	3
63NHG1B-690			63			
80NHG1B-690			80			
100NHG1B-690			100			
125NHG1B-690			125			
160NHG1B-690			160			
63NHG2B-690	gG/gL (Standard)	SD2-D TD2-D	63	690	2	3
80NHG2B-690			80			
100NHG2B-690			100			
125NHG2B-690			125			
160NHG2B-690			160			
200NHG2B-690			200			
224NHG2B-690			224			
250NHG2B-690			250			
315NHG2B-690			315			
250NHG3B-690	gG/gL (Standard)	SD3-D TD3-D	250	690	3	3
315NHG3B-690			315			
355NHG3B-690			355			
400NHG3B-690			400			
500NHG3B-690			500			



NHG1B-690

DIN industrial fuse links - 690V - aM - motor start.						
6NHM000B-690	aM (Motor start)	SD00-D TD00-D	6	690	000	3
10NHM000B-690			10			
16NHM000B-690			16			
20NHM000B-690			20			
25NHM000B-690			25			
32NHM000B-690			32			
40NHM000B-690			40			
50NHM00B-690			50			
63NHM00B-690	aM (Motor start)	SD00-D TD00-D	63	690	00	3
80NHM00B-690			80			
100NHM00B-690			100			
50NHM1B-690	aM (Motor start)	SD1-D TD1-D	50	690	1	3
63NHM1B-690			63			
80NHM1B-690			80			
100NHM1B-690			100			
125NHM1B-690			125			
160NHM1B-690			160			



6NHM000B-690

Downloaded from Arrow.com.

LV Fuse gear


Bussmann series DIN industrial fuses & fuse holders



NHM2B-690



TD00-D



TD00-IP20

Item no.	Type/Description	Fuse holder	Amps	Volts	Size	Box qty
DIN industrial fuse links - 690V - aM - motor start.						
125NHM2B-690	aM (Motor start)	SD2-D TD2-D	125	690	2	3
160NHM2B-690			160			
200NHM2B-690			200			
224NHM2B-690			224			
250NHM2B-690			250			
315NHM2B-690			315			
355NHM2B-690						
250NHM3B-690	aM (Motor start)	SD3-D TD3-D	250	690	3	3
315NHM3B-690			315			
355NHM3B-690			355			
400NHM3B-690			400			
500NHM3B-690			500			

Fuse holders to suit DIN industrial fuse links					
SD00-D	Single pole base	160	690	00	1
SD1-D		250		1	
SD2-D		400		2	
SD3-D		630		3	
TD00-D	Triple pole base	160	690	00	1
TD1-D		250		1	
TD2-D		400		2	
TD3-D		630		3	

FC00	Fuse cover to suit '00'	00	1
FC01	Fuse cover to suit '1'	1	
FC1-2	Fuse cover to suit '2'	2	
FC3	Fuse cover to suit '3'	3	
CS00	Terminal cover '00'	00	1
CS1	Terminal cover '1'	1	
CS2	Terminal cover '2'	2	
CS3	Terminal cover '3'	3	
BC00	Connector "00"	00	1
BC1-2	Connector"1 & 2"	1 & 2	1
BC3	Connector "3"	3	1
TD00-IP20	Triple pole protect kit "00"	00	1
TD1-IP20	Triple pole protect kit "1"	1	1
TD2-IP20	Triple pole protect kit "2"	2	1
TD3-IP20	Triple pole protect kit "3"	3	1
SDL00	Neutral link "00"	00	1
SDL1	Neutral link "1"	1	1
SDL2	Neutral link "2"	2	1
SDL3	Neutral link "3"	3	1
BVL50	Micro switch		1
FEH	Extraction handle		1

Item no.	Description	Poles	Amps	Volts	Size	Box qty
EBH00O3TM8	Horizontal disconnect	3	160	690	00	-
EBH1O3TM1		3	250		1	
EBH2O3TM1		3	400		2	
EBH3O3TM2		3	630		3	

Downloaded from Arrow.com.

LV Fuse gear

D & DO Fuse Links and Fuse Bases

Class gG D and DO fuse links for industrial and domestic applications. All these fuse links incoporate a visual indicator of fuse operation.

Standard:	IEC 60269 and VDE 0636
Rated voltage:	400 and 500Vac
Rated current:	2 to 100A
Breaking capacity:	50kA
Operating class:	Time-delay and ultra-rapid
Sizes:	DI to DV, D01 to D03
Fuse holders:	Available for all fuse links sizes
Applications:	Industrial & commercial (DIN rail mounting with accessories available: screw caps, gauge rings, etc.)



Bussmann series DIN industrial fuses & fuse holders

Item no.	Description	Body dim	Amps	Volts	Size	Box qty
2NZ01	Neozed fuse links	36 X 11mm	2	440	D01	5
4NZ01	Neozed fuse links		4			
6NZ01	Neozed fuse links		6			
10NZ01	Neozed fuse links		10			
16NZ01	Neozed fuse links		16			
20NZ02	Neozed fuse links	36 X 15mm	20	440	D02	5
25NZ02	Neozed fuse links		25			
35NZ02	Neozed fuse links		35			
50NZ02	Neozed fuse links		50			
63NZ02	Neozed fuse links		63			
80NZ03	Neozed fuse links	43 X 22.5mm	80	440	D03	5
100NZ03	Neozed fuse links		100			
2NZ01R	Neozed fuse links - ultra rapid	36 X 11mm	2	440	D01	5
4NZ01R	Neozed fuse links - ultra rapid		4			
6NZ01R	Neozed fuse links - ultra rapid		6			
10NZ01R	Neozed fuse links - ultra rapid		10			
16NZ01R	Neozed fuse links - ultra rapid		16			
20NZ02R	Neozed fuse links - ultra rapid	36 X 15mm	20	440	D02	5
25NZ02R	Neozed fuse links - ultra rapid		25			
35NZ02R	Neozed fuse links - ultra rapid		35			
50NZ02R	Neozed fuse links - ultra rapid		50			
63NZ02R	Neozed fuse links - ultra rapid		63			
2D16	Diazed fuse links - standard	50 x 13mm	2	500	D1	5
4D16	Diazed fuse links - standard		4			
6D16	Diazed fuse links - standard		6			
10D16	Diazed fuse links - standard		10			
16D16	Diazed fuse links - standard		16			
20D16	Diazed fuse links - standard		20			
25D16	Diazed fuse links - standard		25			
2D27	Diazed fuse links - standard	50 x 21.5mm	2	500	D11	5
4D27	Diazed fuse links - standard		4			
6D27	Diazed fuse links - standard		6			
10D27	Diazed fuse links - standard		10			
16D27	Diazed fuse links - standard		16			
20D27	Diazed fuse links - standard		20			
25D27	Diazed fuse links - standard		25			
35D33	Diazed fuse links - standard	50 x 27mm	35	500	D111	5
50D33	Diazed fuse links - standard		50			
63D33	Diazed fuse links - standard		63			
80D125	Diazed fuse links - standard	50 x 33mm	80	500	D1V	1
100D125	Diazed fuse links - standard		100			



NZ01



16D27

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series DIN industrial fuses & fuse holders



6D16Q


25D16R

Item no.	Description	Body dim	Amps	Volts	Size	Box qty
125D200	Diazed fuse links - standard	50 x 46mm	125	500	DV	1
160D200	Diazed fuse links - standard		160			
200D200	Diazed fuse links - standard		200			
2D16Q	Diazed fuse links - quick	50 x 13mm	2	500	D1	5
4D16Q	Diazed fuse links - quick		4			
6D16Q	Diazed fuse links - quick		6			
10D16Q	Diazed fuse links - quick		10			
16D16Q	Diazed fuse links - quick		16			
20D16Q	Diazed fuse links - quick		20			
25D16Q	Diazed fuse links - quick		25			
2D27Q	Diazed fuse links - quick	50 x 21.5mm	2	500	D11	5
4D27Q	Diazed fuse links - quick		4			
6D27Q	Diazed fuse links - quick		6			
10D27Q	Diazed fuse links - quick		10			
16D27Q	Diazed fuse links - quick		16			
20D27Q	Diazed fuse links - quick		20			
25D27Q	Diazed fuse links - quick		25			
35D33Q	Diazed fuse links - quick	50 x 27mm	35	500	D111	5
50D33Q	Diazed fuse links - quick		50			
63D33Q	Diazed fuse links - quick		63			
2D16R	Diazed fuse links - ultra rapid	50 x 13mm	2	500	D1	5
4D16R	Diazed fuse links - ultra rapid		4			
6D16R	Diazed fuse links - ultra rapid		6			
10D16R	Diazed fuse links - ultra rapid		10			
16D16R	Diazed fuse links - ultra rapid		16			
20D16R	Diazed fuse links - ultra rapid		20			
25D16R	Diazed fuse links - ultra rapid		25			
2D27R	Diazed fuse links - ultra rapid	50 x 21.5mm	2	500	D11	5
4D27R	Diazed fuse links - ultra rapid		4			
6D27R	Diazed fuse links - ultra rapid		6			
10D27R	Diazed fuse links - ultra rapid		10			
16D27R	Diazed fuse links - ultra rapid		16			
20D27R	Diazed fuse links - ultra rapid		20			
25D27R	Diazed fuse links - ultra rapid		25			
35D33R	Diazed fuse links - ultra rapid	50 x 27mm	35	500	D111	5
50D33R	Diazed fuse links - ultra rapid		50			
63D33R	Diazed fuse links - ultra rapid		63			

Fuse bases & gauge rings are available, please contact customer sevice - 02 8787 2730.

Downloaded from Arrow.com.

LV Fuse gear

North American Fuse Links and Fuse Holderss

Standard:	UL Listed and CSA Certified
Rated voltage:	Up to 600Vac
Rated current:	0.1 to 6000A
Breaking capacity:	Up to 300kA
Operating class:	Time-delay, fast-acting as per UL requirements
Sizes:	Midget, Class CC, G, H, J, K5, H, L, RK5, RK1 and T
Fuse holders:	Modular Fuse Holder (finger protection) for Midget and Class CC fuse links Finger-safe protected fuse base for Class J fuse links
Applications:	Suitable for applications or equipments to be exported to the USA or other UL markets



Bussmann series North American fuse links & fuse holders.

Item no.	Amp rating	Size	Volts	Type	Box qty
Supplementary power fuse links (ferrule)					
BBS (A)	1/10 to 5	10 x 35mm	600	Fast	10
	6, 7, 8, 10		250		
	12, 15, 20, 25, 30		48		
KTQ (A)	1, 1.6, 2, 3, 4, 5, 6		250	T/Delay	
BAF (A)	2/10 to 15	10 x 38mm	250	Fast	10
	20, 25, 30		125		
BAN (A)	1, 2, 4, 6, 8, 10, 12, 15, 20, 25, 30		250	Fast	
KTK (A)	1/10 to 50		600	Fast	
DCM (A)	1/10 to 30		600V ac / dc	Fast	
KLM (A)	1/10 to 30		690	Fast	
FNM (A)	0.1, 0.125, 0.15, 0.2, 0.25, 0.3, 0.4, 0.5, 0.6, 0.75, 1, 1.125, 1.25, 1.5, 2, 2.25, 2.5, 2.8, 3, 3.25, 3.5, 4, 4.5, 5, 5.8, 6, 6.25, 7, 8, 9, 10,		250	T/Delay	
	12, 15		125		
	20, 25, 30		32		
FNQ (A)	1/10 to 30		500	T/Delay	
FNA (A)	1/10 to 8/10		250	T/Delay	
	1 to 15		125		
	20 to 30		32		
DMM-D-(A)	44/100 & 11		1000	Fast	
Supplementary power fuse links - rejection - Class CC.					
KTK-R (A)	1/10 to 30	10 X 38mm	600	Fast	10
LP-CC (A)	1/4 to 30			T/Delay	
FNQ-R (A)	1/4 to 30				
Supplementary power fuse links - Class G.					
SC	1/2 to 20	10 X 33	480	T/Delay	
	25, 30	10 X 42			
	35 to 60	10 X 57			



BAF



FNA



KTK-R

Item no.	Amp	Volts	Poles	Box qty
Fuseholders to suit supplementary power fuse links.				
BM6031SQ	30	600	1	1
BM6033SQ			3	
Fuseholders to suit supplementary power fuse links - Class CC.				
BC6031SQ	30	600	1	1
BC6033SQ			3	



SC

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series North American fuse links & fuse holders.



JJN



JJS



T60030-3CR



H30100-1SR

Item no.	Amp rating	Size	Volts	Type	Box qty
Power fuse links - Class T.					
JJN (A)	1, 2, 3, 6, 10, 15, 20, 25, 30	22 X 10	300	Very Fast	10
	35, 40, 45, 50, 60	23 X 14			
	70, 80, 90, 100	40.0	300	Very Fast	1
	110, 125, 150, 175, 200	43.0			
	225, 250, 300, 350, 400	47.0			
	450, 500, 600	52.0			
	700, 800	56.0			
	1000, 1200	64.0			
JJS (A)	1, 2, 3, 6, 10, 15, 20, 25, 30	38 X 14	600	Very Fast	10
	35, 40, 45, 50, 60	40 X 21			
	70, 80, 90, 100	60.0	600	Very Fast	1
	110, 125, 150, 175, 200	64.0			
	225, 250, 300, 350, 400	69.0			
	450, 500, 600	75.0			
	800	81.0			
Power fuse links - general purpose					
NON (A)	0.125, 0.5, .75, 1, 1.5, 2, 2.5, 3, 4, 5, 6, 7, 8, 10,12, 15, 20, 25, 30	10 x 51	250	Non Delay	10
	35, 40, 45, 50, 60	21 x 76			
	70, 80, 90, 100	149.0	250	Non Delay	1
	110, 125, 150, 175, 200	181.0			
	225, 250, 300, 350, 400	219.0			
	450, 500, 600	264.0			
NOS (A)	1, 2, 2.5, 3, 4, 5, 6, 7, 8, 10, 12, 15, 20, 25, 30	21 x 127	600	Non Delay	10
	35, 40, 45, 50, 60	27 x 140			
	70, 80, 90, 100	200.0	600	Non Delay	1
	110, 125, 150, 175, 200	244.0			
	225, 250, 300, 350, 400	295.0			
	450, 500, 600	340.0			

Item no.	Amp	Volts	Poles	Box qty
Fuse holders to suit power fuse links - Class T.				
T30030-2CR	30	300	2	1
T30030-3CR			3	
T30060-2CR	60	300	2	
T30060-3CR			3	
T30100-1CR	100	300	1	
T30100-3CR			3	
T60030-1CR	30	600	1	
T60030-3CR			3	
T60060-1CR	60	600	1	
T60060-3CR			3	
T60100-1CR	100	600	1	
T60100-3CR			3	
Fuse holders to suit power fuse links - general purpose.				
H30030-2SR	30	300	1	1
H30030-3SR			3	
H30060-2SR	60	300	2	
H30060-3SR			3	
H30100-1SR	100	300	1	
H30100-3SR			3	
H60030-1SR	30	600	1	
H60030-3SR			3	
H60060-1SR	60	600	1	
H60060-3SR			3	
H60100-1SR	100	600	1	
H60100-3SR			3	

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series North American fuse links & fuse holders.

Item no.	Amp rating	Size	Volts	Type	Box qty
Power fuse links - Class RK1.					
LPN-RK (A) SP	1/10 to 30	14 x 51	250	Dual element, time delay	10
	35, 40, 45, 50, 60	21 x 76			
	70, 80, 90, 100	149.0	250		1
	110, 125, 150, 175, 200	181.0			
	225, 250, 300, 350, 400	219.0			
	450, 500, 600	264.0			
LPS-RK (A) SP	1/10 to 30	21 X 127	600	Dual element, time delay	10
	35, 40, 45, 50, 60	27 X 140			
	70, 80, 90, 100	200.0	600		1
	110, 125, 150, 175, 200	245.0			
	225, 250, 300, 350, 400	295.0			
	450, 500, 600	340.0			
KTN-R (A)	1 to 30	14 x 51	250	Fast acting	10
	35, 40, 45, 50, 60	21 x 76			
	70, 80, 90, 100	149.0	250		1
	110, 125, 150, 175, 200	181.0			
	225, 250, 300, 350, 400	219.0			
	450, 500, 600	264.0			
KTS-R (A)	1 to 30	21 X 127	600	Fast acting	10
	35, 40, 45, 50, 60	27 X 140			
	70, 80, 90, 100	200.0	600		1
	110, 125, 150, 175, 200	245.0			
	225, 250, 300, 350, 400	295.0			
	450, 500, 600	340.0			
FRN-R (A)	100mA to 30A	14 x 51	250	Dual element, time delay	10
	35, 40, 45, 50, 60	21 x 76			
	70, 80, 90, 100	149.0	250		1
	110, 125, 150, 175, 200	181.0			
	225, 250, 300, 350, 400	219.0			
	450, 500, 600	264.0			
FRS-R (A)	100mA to 30A	21 X 127	600	Dual element, time delay	10
	35, 40, 45, 50, 60	27 X 140			
	70, 80, 90, 100	200.0	600		1
	110, 125, 150, 175, 200	245.0			
	225, 250, 300, 350, 400	295.0			
	450, 500, 600	340.0			
Power fuse links - Class J low peak.					
LPJ- (A) SP	1 to 30	21 X 58	600	Dual element, time delay	10
	35, 40, 45, 50, 60	27 X 60			
	70, 80, 90, 100	92.0	600		1
	110, 125, 150, 175, 200	111.0			
	225, 250, 300, 350, 400	133.0			
	450, 500, 600				
JKS- (A)	1 to 30	21 X 58	600	Quick acting	10
	35, 40, 45, 50, 60	27 X 60			
	70, 80, 90, 100	92.0	600		1
	110, 125, 150, 175, 200	111.0			
	225, 250, 300, 350, 400	133.0			
	450, 500, 600	152.0			


LPN-RK


LPS-RK


KTN-R


KTS-R


FRN-R


FRS-R


LPJ


JKS

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series North American fuse links & fuse holders.



KTU



KRP-C

Item no.	Amp rating	Size	Volts	Type	Box qty
Power fuse links - Class L low peak.					
KTU (A)	601 to 1200	Contact cooper electrical for size	600	Fast acting type	1
	1500, 2000				
	2500, 3000				
	3500, 4000				
	4500, 5000				
	6000				
KLU (A)	601 to 1200	Contact cooper electrical for size	600	Time delay type	
	1500, 1600				
	1800, 2000				
	2500, 3000				
	4000				
KRP-C (A) SP	601 to 1200	Contact cooper electrical for size	600	Time delay type	
	1350, 1400, 1500, 1600, 1800, 1900, 2000				
	2001, 2400, 2500, 3000				
	3500, 3800, 4000				
	4500, 5000				
	6000				



R300



J600

Item no.	Amp	Volts	Poles	Box qty
Fuse holders to suit power fuse links - Class RK1 & RK5.				
R30030-1SR	30	300	1	1
R30030-3SR			3	
R30060-2CR	60	300	2	
R30060-3CR			3	
R30100-1CR	100	300	1	
R30100-3CR			3	
R60030-1CR	30	600	1	
R60030-3CR			3	
R60060-1CR	60	600	1	
R60060-3CR			3	
R60100-1CR	100	600	1	
R60100-3CR			3	
Fuse holders to suit power fuse links - Class RK1 & RK5.				
J60030-1CR	30	600	1	1
J60030-3CR			3	
J60060-1CR	60	600	1	
J60060-3CR			3	
J60100-1CR	100	600	1	
J60100-3CR			3	

Downloaded from Arrow.com.

LV Fuse gear



Ferrule Style Fuse Links

Standard:	UL/CSA
Rated voltage:	700Vac. DC ratings available
Rated current:	1 to 100A
Breaking capacity:	20kA
Operating class:	aR
Sizes:	From to 6x32 to 25x146mm
Applications:	Used for the protection of DC common bus, DC drives, power converters/ rectifiers and reduced voltage starters

Bussmann series high speed fuse links.

Item no.	Description	Body dim	Amps	Volts	I²T	Box qty
High speed fuse links - ferrule type.						
FWA-5A10F		10 x 38mm	5	150 Vac / Vdc	8	10
FWA-10A10F			10		16	
FWA-15A10F			15		55	
FWA-20A10F			20		130	
FWA-25A10F			25		220	
FWA-30A10F			30		400	
FWA-35A21F		21 x 51mm	35	150 Vac / Vdc	800	10
FWA-40A21F			40		1000	
FWA-45A21F			45		1300	
FWA-50A21F			50		1600	
FWA-60A21F			60		2400	
FWX-1A14F		14 x 51mm	1	250 Vac / Vdc	0.4	10
FWX-2A14F			2		0.1	
FWX-3A14F			3		0.26	
FWX-4A14F			4		0.23	
FWX-5A14F			5		13	
FWX-10A14F			10		24	
FWX-15A14F			15		83	
FWX-20A14F			20		200	
FWX-25A14F			25		300	
FWX-30A14F			30		500	
FWX-50A14F			50		1800	
FWH-.250A6F		6.3 x 32mm	0.25	500 Vac	0.05	10
FWH-.500A6F			0.5		0.25	
FWH-001A6F			1		2	
FWH-002A6F			2		3.5	
FWH-3.15A6F			3.15		7.7	
FWH-005A6F			5		40	
FWH-6.30A6F			6.3		90	
FWH-007A6F			7		125	
FWH-010A6F			10		51	
FWH-12.5A6F			12.5		60	
FWH-015A6F			15		146	
FWH-016A6F			16		177	
FWH-020A6F			20		259	
FWH-025A6F			25		345	
FWH-030A6F			30		430	



FWA-5A10F



FWA-45A21F



FWX-15A14F

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.


FWH-.500A6F


FWC-6A10F


FWP-1A14F


FWP-25A22F

Item no.	Description	Body dim	Amps	Volts	I²T	Box qty
High speed fuse links - ferrule type.						
FWH-1A14F		14 x 51mm	1	500 Vac/ Vdc	0.04	10
FWH-2A14F			2		0.1	
FWH-3A14F			3		0.23	
FWH-4A14F			4		0.23	
FWH-5A14F			5		6.4	
FWH-6A14F			6		6.4	
FWH-10A14F			10		13	
FWH-12A14F			12		-	
FWH-15A14F			15		40	
FWH-20A14F			20		105	
FWH-25A14F			25		191	
FWH-30A14F			30		232	
FWC-6A10F		10 x 38mm	6	600 Vac / Vdc	30	10
FWC-8A10F			8		50	
FWC-10A10F			10		70	
FWC-12A10F			12		120	
FWC-16A10F			16		150	
FWC-20A10F			20		260	
FWC-25A10F			25		390	
FWC-30A10F			32		600	
FWP-1A14F		14 x 51	1	700 Vac / Vdc	0.41	10
FWP-2A14F			2		0.11	
FWP-2.5A14F			2.5		-	
FWP-3A14F			3		0.26	
FWP-4A14F			4		0.23	
FWP-5A14F			5		11	
FWP-10A14F			10		22	
FWP-15A14F			15		75	
FWP-20A14F			20		180	
FWP-25A14F			25		320	
FWP-30A14F			30		450	
FWP-32A14F			32		600	
FWP-40A14F			40		750	
FWP-50A14F			50		1800	
FWP-20A22F		22 x 58	20	700 Vac / Vdc	260	
FWP-25A22F			25		410	
FWP-32A22F			32		605	
FWP-40A22F			40		750	
FWP-50A22F			50		1600	
FWP-63A22F			63		3080	
FWP-80A22F			80		6600	
FWP-100A22F			100		12500	
FWP-10A14FI	With indicator	14 x 51	10	700 Vac / Vdc	22	10
FWP-15A14FI			15		75	
FWP-20A14FI			20		180	
FWP-25A14FI			25		320	
FWP-30A14FI			30		450	
FWP-32A14FI			32		600	
FWP-40A14FI			40		750	
FWP-50A14FI			50		1800	

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.

Item no.	Description	Body dim	Amps	Volts	I²T	Box qty
High speed fuse links - ferrule type.						
FWP-20A22FI	With indicator	22 x 58	20	700 Vac / Vdc	260	10
FWP-25A22FI			25		410	
FWP-32A22FI			32		605	
FWP-40A22FI			40		750	
FWP-50A22FI			50		1600	
FWP-63A22FI			63		3080	
FWP-80A22FI			80		6600	
FWP-100A22FI			100		12500	
FWJ-20A14F		14 x 67		1000Vac / 800Vdc		10
FWJ-25A14F						
FWJ-30A14F						
FWS-2A20F		20 x 127mm	2	2000Vac 1000Vdc	2.4	10
FWS-6A20F			6		81	
FWS-8A20F			8	1500Vac 1000Vdc	192	
FWS-10A20F			10		277	
FWS-12A20F			12		380	
FWS-15A20F			15		500	
FWL-20A20F			20	1250Vac 1000Vdc	1550	
FWL-25A20F			25		2760	
FWL-30A20F			30		4300	
FWS-2A20FI	With indicator	20 x 127mm	2	2000Vac 1000Vdc	2.4	10
FWS-6A20FI			6		81	
FWS-8A20FI			8	1500Vac 1000Vdc	192	
FWS-10A20FI			10		277	
FWS-12A20FI			12		380	
FWS-15A20FI			15		500	
FWL-20A20FI			20	1250Vac 1000Vdc	1550	
FWL-25A20FI			25		2760	
FWL-30A20FI			30		4300	



FWJ-25A14F



FWS-6A20F



FWS-12A20FI

Downloaded from Arrow.com.



LV Fuse gear

British Standard high speed Fuse Links

Standard:	BS88 part 4 and IEC 60269-4
Rated voltage:	240 and 690Vac
Rated current:	6 to 710A
Breaking capacity:	200kA
Operating class:	aR
Sizes:	Refer to relevant data sheets, available upon request
Applications:	Used for the protection of DC common bus, DC drives, power converters/ rectifiers and reduced voltage starters

Bussmann series high speed fuse links.



10LTC


100LET


400LMMT


20CT

Item no.	Description	Fix ctrs	Amps	Volts	I^2T	Box qty
High speed fuse links - British standard.						
6LCT	GSA5	38mm	6	240Vac 150Vdc	9	10
10LCT	GSA10		10		22	
12LCT			12		32	
16LCT	GSA15		16		100	
20LCT	GSA20		20		160	
25LET	GSA25	42mm	25	240Vac 150Vdc	250	10
32LET			32		450	
35LET	GSA35		35		600	
50LET	GSA50		50		1400	
63LET			63		2200	
80LET	GSA75		80		3800	
100LET	GSA100		100		7500	
125LET			125		7500	
160LET			160		16000	
180LET			180		29000	
160LMT	GSA150	59mm	160	240Vac 150Vdc	16000	1
200LMT	GSA200		200		20000	
250LMT	GSA50		250		40000	
315LMT	GSA300		315		75000	
355LMT	GSA350		355		100000	
400LMT	GSA400		400		160000	
450LMT			450		220000	
400LMMT		59mm	400	240Vac 150Vdc	80000	1
500LMMT	GSA500		500		170000	
630LMMT	GSA630		630		300000	
710LMMT			710		460000	
800LMMT			800		600000	
900LMMT			900		800000	
6CT	GSB5	64mm	6	690Vac 500Vdc	12	20
10CT	GSB10		10		48	
12CT			12		65	
16CT	GSB15		16		110	
20CT	GSB20		20		220	

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.

Item no.	Description	Fix ctrs	Amps	Volts	I²T	Box qty
High speed fuse links - British standard.						
25ET	GSB25	64mm	25	690Vac 500Vdc	250	10
32ET	GSGB30		32		350	
35ET	GSGB35		35		500	
40ET	GSGB40		40		900	
45ET	GSB45		45		1100	
56ET	GSGB55		56		1500	
63ET	GSGB63		63		2000	
80ET	GSGB80		80		4000	
35FE	GSGB35	64mm	35	690Vac 500Vdc	200	10
40FE	GSGB40		40		300	
45FE	GSGB45		45		450	
50FE	GSGB50		50		600	
63FE	GSGB55		63		750	
71FE			71		950	
80FE	GSGB80		80		1500	
90FE	GSGB85		90		2100	
100FE			100		2800	
75EET	GSGB75	70mm	75	690Vac 500Vdc		5
90EET	GSGB85		90		4500	
110EET	GSGB110		110		6500	
140EET	GSGB150		140		12000	
160EET	GSG160		160		17000	
100FEE		70mm	100	690Vac 500Vdc	2400	5
120FEE	GSGB125		120		3100	
140FEE	GSGB125		140		3800	
160FEE	GSGB160		160		5700	
180FEE			180		8400	
200FEE			200		11400	
180FM	GSGB170	85mm	180	690Vac 500Vdc	13500	1
200FM	GSGB200		200		18500	
225FM	GSGB225		225		26500	
250FM	GSGB250		250		37500	
280FM			280		55000	
315FM	GSGB315		315		77000	
350FM	GSGB325		350		105000	
400FMM	GSGB400	85mm	400	690Vac 500Vdc	72500	1
450FMM			450		105000	
500FMM	GSGB500		500		150000	
550FMM			550		215000	
630FMM			630		310000	
700FMM			700		420000	



35ET



90EET



180FM



400FMM

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.



200MT



315MMT

Item no.	Description	Fix ctrs	Amps	Volts	I²T	Box qty
High speed fuse links - British standard.						
165MT	GSGB150	85mm	160	690Vac 350Vdc	25000	
180MT			180		38000	
200MT	GSGB200		200		58000	
250MT	GSGB250		250		110000	
280MT			280		150000	
315MT			315		180000	
355MT			355		200000	
180MMT		85mm	180	690Vac 350Vdc	18000	
200MMT			200		23000	
250MMT			250		40000	
280MMT			280		70000	
315MMT			315		91000	
355MMT			355		140000	
400MMT	GSGB400		400		220000	
450MMT	GSGB450		450		320000	
500MMT	GSGB500		500		450000	
550MMT			550		640000	
630MMT			630		720000	
700MMT			700		850000	
High speed fuse links - British standard accessories.						
MAI	Microswitch and Adaptor			250		1
MC-250	Trip Indicator Fuse Link and clips to suit LMT LMMT					
MC-600	Trip Indicator Fuse Link and clips to suit FM FMM					
MCLIP	Clips to suit FM FMM LMT LMMT					
TI250	Trip Indicator Fuse			250		1
TI500	Trip Indicator Fuse			500		
TI600	Trip Indicator Fuse			600		
TI700	Trip Indicator Fuse			700		
TI1100	Trip Indicator Fuse			1100		
TI2000	Trip Indicator Fuse			1200		
TI1500	Trip Indicator Fuse			1500		
TI2500	Trip Indicator Fuse			2500		
LSCR1-K	General Purpose Fuse Blocks		400	1000		2
LSCR2-K			800			

Downloaded from Arrow.com.

LV Fuse gear



North American hi speed Fuse Links

Standard:	UL/CSA
Rated voltage:	Up to 600Vac
Rated current:	1 to 6000A
Breaking capacity:	200kA
Operating class:	Fast acting
Sizes:	Refer to relevant data sheets, available upon request
Applications:	Suitable for medium power applications for UL markets

Bussmann series high speed fuse links.

Item no.	Description	Fix ctrs	Amps	Volts	I^2T	Box qty
High speed fuse links - North American standard.						
FWA -70B	A15QS L15S	52mm	70	150 Vac / Vdc	4000	1
FWA -80B			80		6000	
FWA -100B			100		12000	
FWA -125B			125		18000	
FWA -150B			150		26000	
FWA -200B			200		45000	
FWA-225B			225		-	
FWA -250B			250		70000	
FWA -300B			300		100000	
FWA -350B			350		140000	
FWA -400B			400		180000	
FWA -450B	A15QS L15S	62mm	450	150 Vac / Vdc	-	1
FWA -500A			500		120000	
FWA -600A			600		140000	
FWA -700A			700		220000	
FWA -800A			800		280000	
FWA -1000A			1000		510000	
FWA-1000AH		48 x 51	1000	150 Vac / Vdc	460000	
FWA-1200AH			1200		730000	
FWA-1500AH			1500		1400000	
FWA-2000AH			2000		2400000	
FWA-2500AH		48 X 75	2500		4100000	
FWA-3000AH			3000		5700000	
FWA-4000AH		48 x 89	4000		9200000	
FWX-35A	A30QS A25P(A)-4 L25S	61mm	35	250 Vac / Vdc	230	1
FWX-40A			40		310	
FWX-45A			45		390	
FWX-50A			50		520	
FWX-60A			60		740	
FWX-70A		58mm	70		1400	
FWX-80A			80		1850	
FWX-90A			90		2450	
FWX-100A			100		3150	
FWX-125A			125		4850	
FWX-150A			150		6950	
FWX-175A			175		9300	
FWX-200A			200		12000	



FWA-400B



FWA-20000AH



FWX-600A



FWX-160AH

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.



FWX-160AH

Item no.	Description	Fix ctrs	Amps	Volts	I²T	Box qty
High speed fuse links - North American standard.						
FWX-225A	A30QS A25P(A)-4 L25S	66mm	225	250 Vac / Vdc	14700	1
FWX-250A			250		18100	
FWX-275A			275		21600	
FWX-300A			300		27300	
FWX-350A			350		48600	
FWX-400A			400		66100	
FWX-450A			450		101000	
FWX-500A			500		128000	
FWX-600A			600		188000	
FWX-700A		69mm	700		190000	
FWX-800A			800		230000	
FWX-1000AH		66 x 89	1000		360000	
FWX-1200AH			1200		750000	
FWX-1500AH		66 x 75	1500	250 Vac / Vdc	880000	
FWX-1600AH			1600		1200000	
FWX-2000AH			2000		2300000	
FWX-2500AH			2500		4700000	



FWH-150B

FWH-35B	A50QS A50P L50S	58mm	35	500 Vac / Vdc	150	
FWH-40B		58mm	40		320	
FWH-45B		58mm	45		450	
FWH-50B		58mm	50		670	
FWH-60B		58mm	60		900	
FWH-70B		73mm	70		900	
FWH-80B		73mm	80		1400	
FWH-90B		73mm	90		1600	
FWH-100B		73mm	100		2000	
FWH-125B		73mm	125		3500	
FWH-150B		73mm	150		4600	
FWH-175B		73mm	175		6200	
FWH-200B		73mm	200		8500	
FWH-225A	A50QS A50P L50S	77mm	225	500 Vac / Vdc	23300	
FWH-250A		77mm	250		32200	
FWH-275A		77mm	275		40300	
FWH-300A		77mm	300		49800	
FWH-325A		77mm	325		63800	
FWH-350A		77mm	350		72900	
FWH-400A		77mm	400		96700	
FWH-450A		81mm	450		127000	
FWH-500A		81mm	500		149000	
FWH-600A		81mm	600		206000	
FWH-700A		108mm	700		298000	
FWH-800A		108mm	800		409000	
FWH-1000A		126mm	1000		450000	
FWH-1200A		126mm	1200		600000	
FWH-1400A		158 / 228 mm	1400		1000000	
FWH-1600A		158 / 228 mm	1600		1400000	

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.

Item no.	Description	Fix ctrs	Amps	Volts	I²T	Box qty
High speed fuse links - North American standard.						
FWP-5B	A70QS A70P L70S	64mm	5	700 Vac / Vdc	10	
FWP-10B		64mm	10		20	
FWP-15B		64mm	15		75	
FWP-20B		64mm	20		180	
FWP-25B		64mm	25		340	
FWP-30B		64mm	30		450	
FWP-35B		89mm	35		160	
FWP-40B		89mm	40		320	
FWP-50B		89mm	50		600	
FWP-60B		89mm	60		950	
FWP-70B		98mm	70		2000	
FWP-80B		98mm	80		2400	
FWP-90B		98mm	90		2700	
FWP-100B		98mm	100		3500	
FWP-125A		98mm	125		7300	
FWP-150A		98mm	150		11700	
FWP-175A	A70QS A70P L70S	98mm	175	700 Vac / Vdc	16700	
FWP-200A		98mm	200		22000	
FWP-225A		98mm	225		31300	
FWP-250A		98mm	250		42500	
FWP-300A		98mm	300		71200	
FWP-350A		98mm	350		95600	
FWP-400A		98mm	400		125000	
FWP-450A		127mm	450		137000	
FWP-500A		127mm	500		170000	
FWP-600A		127mm	600		250000	
FWP-700A		133mm	700		300000	
FWP-800A		133mm	800		450000	
FWP-900A		140mm	900		530000	
FWP-1000A		140mm	1000		600000	
FWP-1200A		174 / 224mm	1200		1100000	



FWP-400A

FWJ-35A	A100P	109mm	35	1000 Vac / 800Vdc	2000	
FWJ-40A		109mm	40		2500	
FWJ-50A		109mm	50		3500	
FWJ-60A		109mm	60		5000	
FWJ-70A		109mm	70		6900	
FWJ-80A		109mm	80		9700	
FWJ-90A		109mm	90		12000	
FWJ-100A		109mm	100		17500	
FWJ-125A		112mm	125		35000	
FWJ-150A		112mm	150		45000	
FWJ-175A		112mm	175		65000	
FWJ-200A		112mm	200		80000	
FWJ-250A		112mm	250		112000	
FWJ-300A		112mm	300		164000	
FWJ-350A		112mm	350		231000	
FWJ-400A		112mm	400		330000	
FWJ-500A		130mm	500		329000	
FWJ-600A		130mm	600		520000	
FWJ-800A		130mm	800		500000	
FWJ-1000A		135mm	1000		1100000	
FWJ-1200A		135mm	1200		2100000	
FWJ-1400A		135mm	1400		2700000	
FWJ-1600A		135mm	1600		4000000	
FWJ-1800A		135mm	1800		5300000	
FWJ-2000A		135mm	2000		7600000	



FWJ-300A

Downloaded from Arrow.com.

LV Fuse gear



Square Body Fuse Links

A square bodied range of industrial fuse links for a wide variety of applications.
NH fuse bases with thermoplastic bodies, DIN rail and/or screw mounting (size 4 screw mounting only).
Range of accessories including phase barriers, IP20 finger-safe protection kits and neutral links available.

Standard:	IEC 60269-4, DIN 43653 and 43620, UL Recognition and CSA Component acceptance
Rated voltage:	690 and 1250Vac, higher voltage ratings available
Rated current:	10 to 7500A
Breaking capacity:	Up to 300kA
Operating class:	aR
Sizes:	000, 00, 1 to 5
Applications:	Used for the protection of DC common bus, DC drives, power converters/ rectifiers and reduced voltage starters. Customs solutions also available

Bussmann series high speed fuse links.



170M1558D



170M3808D



170M5808D

Item no.	Description		Size	Amps	Volts	I²T	Box qty
High speed fuse links - DIN standard - blade - aR.							
170M1558D	aR		000	10	690	25.5	10
170M1559D				16		48	
170M1560D				20		78	
170M1561D				25		130	
170M1562D				32		270	
170M1563D				40		460	
170M1564D				50		770	
170M1565D				63		1450	
170M1566D				80		2550	
170M1567D				100		4650	
170M1568D				125		8500	
170M1569D				160		16000	
170M1570D				200		28000	
170M1571D				250		51500	
170M1572D	aR		00	315	690	80500	10
170M3808D	aR		1	40	690	285	
170M3809D				50		550	
170M3810D				63		850	
170M3811D				80		1350	
170M3812D				100		2600	
170M3813D				125		3900	
170M3814D				160		8250	
170M3815D				200		16500	
170M3816D				250		31000	
170M3817D				315		52000	
170M3818D				350		73000	
170M3819D				400		115000	
170M4863D				450		155000	
170M4864D				500		190000	
170M4865D				550		240000	
170M4866D				630		345000	
170M4867D				700		495000	
170M5808D	aR		2	400	690	79000	
170M5809D				450		115000	
170M5810D				500		155000	
170M5811D				550		215000	
170M5812D				630		295000	
170M5813D				700		430000	
170M5814D				800		610000	
170M5815D				900		895000	
170M5816D				1000		1300000	
170M5817D				1100		1750000	

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.

Item no.	Description	Size	Amps	Volts	I²T	Box qty
170M6808D	aR	3	500	690	99500	
170M6809D			550		140000	
170M6810D			630		220000	
170M6811D			700		320000	
170M6812D			800		490000	
170M6813D			900		720000	
170M6814D			1000		985000	
170M6892D			1100		1400000	
170M8554D			1250		2150000	
170M8555D			1400		2700000	
170M8556D			1500		3350000	
170M8557D			1600		4150000	



170M6808D

High speed fuse links - DIN standard - blade - gR.						
170M2691	gR	00	10	690	20	
170M2692			16		38	
170M2693			20		70	
170M2694			25		125	
170M2695			32		275	
170M2696			40		490	
170M2697			50		1000	
170M2698			63		1800	
170M2699			80		3600	
170M2700			100		6650	
170M2701			125		12000	
170M2702			160		22500	



170M2691

170M4176	gR	1	50	690	705	
170M4177			63		1300	
170M4178			80		2600	
170M4179			100		4850	
170M4180			125		9500	
170M4181			160		18000	
170M4182			200		34500	
170M4183			250		70500	
170M4184			315		135000	
170M4185			350		175000	
170M4186			400		250000	



170M4176

170M5881	gR	2	200	690	29000	
170M5882			250		52500	
170M5883			315		105000	
170M5884			350		135000	
170M5885			400		205000	
170M5886			450		290000	
170M5887			500		375000	
170M5888			550		515000	
170M5889			630		770000	



170M5881

170M6080	gR	3	350	690	120000	
170M6081			400		175000	
170M6082			450		250000	
170M6083			500		330000	
170M6084			550		435000	
170M6085			630		645000	
170M6086			700		840000	
170M6087			800		1300000	



170M6080

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.



170M1480



170M4116



170M5108

Item no.	Description		Size	Amps	Volts	I²T	Box qty
High speed fuses - DIN standard - 80mm fixing.							
170M1408				10		25.5	
170M1409				16		48	
170M1410				20		78	
170M1411				25		130	
170M1412				32		270	
170M1413				40		460	
170M1414				50		770	
170M1415	aR		000	63	690	1450	
170M1416				80		2550	
170M1417				100		4650	
170M1418				125		8500	
170M1419				160		16000	
170M1420				200		28000	
170M1421				250		51500	
170M1422				315		80500	
170M2670	aR		00	350	690	91500	
170M2671				400		125000	
170M3108				40		270	
170M3109				50		515	
170M3110				63		770	
170M3111				80		1250	
170M3112				100		2450	
170M3113				125		3700	
170M3114				160		7500	
170M3115	aR		1*	200	690	15000	
170M3116				250		28500	
170M3117				315		46500	
170M3118				350		68500	
170M3119				400		105000	
170M3120				450		140000	
170M3121				500		180000	
170M3122				550		230000	
170M3123				630		325000	
170M4108				200		11500	
170M4109				250		21000	
170M4110				315		42000	
170M4111				350		59000	
170M4112				400		91500	
170M4113	aR		1	450	690	120000	
170M4114				500		170000	
170M4115				550		230000	
170M4116				630		350000	
170M4117				700		465000	
170M4118				800		725000	
170M4119	aR		1	900	550	850000	
170M5108				400		74000	
170M5109				450		105000	
170M5110				500		145000	
170M5111				550		190000	
170M5112				630		275000	
170M5113	aR		2	700	690	405000	
170M5114				800		575000	
170M5115				900		840000	
170M5116				1000		1250000	
170M5117				1100		1600000	
170M5118				1250		2400000	

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.

Item no.	Description	Size	Amps	Volts	I²T	Box qty
High speed fuses - DIN standard - 80mm fixing.						
170M6108	aR	3	500	690	95000	
170M6109			550		135000	
170M6110			630		210000	
170M6111			700		300000	
170M6112			800		465000	
170M6113			900		670000	
170M6114			1000		945000	
170M6115			1100		1300000	
170M6116			1250		1950000	
170M6117			1400		2450000	
170M6118			1500		3100000	
170M6119			1600		3900000	
170M6120	aR	3	1800	600	5250000	
170M6121	aR	3	2000	550	6350000	



170M6109

High speed fuses - DIN standard - 110mm fixing.						
170M3258	aR	1*	40	690	270	
170M3259			50		515	
170M3260			63		770	
170M3261			80		1250	
170M3262			100		2450	
170M3263			125		3700	
170M3264			160		7500	
170M3265			200		15000	
170M3267			250		28500	
170M3268			315		46500	
170M3269			350		68500	
170M3270			400		105000	
170M3271			450		140000	
170M3272			500		180000	
170M3273			550		230000	
170M3274			630		325000	



170M3258

170M4258	aR	1	200	690	11500	
170M4259			250		21000	
170M4260			315		42000	
170M4261			350		59000	
170M4262			400		91500	
170M4263			450		120000	
170M4264			500		170000	
170M4265			550		230000	
170M4266			630		350000	
170M4267			700		465000	
170M4268			800		725000	
170M4269	aR	1	900	550	850000	



170M4258

170M5258	aR	2	400	690	74000	
170M5259			450		105000	
170M5260			500		145000	
170M5261			550		190000	
170M5262			630		275000	
170M5263			700		405000	
170M5264			800		575000	
170M5265			900		840000	
170M5266			1000		1250000	
170M5267			1100		1600000	
170M5268			1250		2400000	

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.



170M5258



170M6258



170M2758



170M3462

Item no.	Description		Size	Amps	Volts	I²T	Box qty
High speed fuses - DIN standard - 110mm fixing.							
170M6258	aR		3	500	690	95000	
170M6259				550		135000	
170M6260				630		210000	
170M6261				700		300000	
170M6262				800		465000	
170M6263				900		670000	
170M6264				1000		945000	
170M6265				1100		1300000	
170M6266				1250		1950000	
170M6267				1400		2450000	
170M6268				1500		3100000	
170M6269				1600		3900000	
170M6270	aR		3	1800	600	5250000	
170M6271	aR		3	2000	550	6350000	
High speed fuse links - DIN standard - flush end contact.							
170M2758	aR		00	25	690	130	
170M2759				32		270	
170M2760				40		460	
170M2761				50		770	
170M2762				63		1450	
170M2763				80		2550	
170M2764				100		4650	
170M2765				125		8500	
170M2766				160		16000	
170M2767				200		28000	
170M2768				250		51500	
170M2769				315		80500	
170M2770				350		91500	
170M2771				400		125000	
High speed fuse links - DIN standard - flush end contact.							
170M3458	aR		1*	40	690	270	
170M3459				50		515	
170M3460				63		770	
170M3461				80		1250	
170M3462				100		2450	
170M3463				125		3700	
170M3464				160		7500	
170M3465				200		15000	
170M3466				250		28500	
170M3467				315		46500	
170M3468				350		68500	
170M3469				400		105000	
170M3470	aR		1	450	690	140000	
170M3471				500		180000	
170M3472				550		230000	
170M3473				630		325000	
170M4458				200		11500	
170M4459				250		21000	
170M4460				315		42000	
170M4461				350		59000	
170M4462				400		91500	
170M4463				450		120000	
170M4464				500		170000	
170M4465				550		230000	
170M4466				630		350000	
170M4467				700		465000	
170M4468				800		725000	

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series high speed fuse links.

Item no.	Description	Size	Amps	Volts	I²T	Box qty
High speed fuse links - DIN standard - flush end contact.						
170M4469	aR	1	900	550	850000	
170M5458	aR	2	400	690	74000	
170M5459			450		105000	
170M5460			500		145000	
170M5461			550		190000	
170M5462			630		275000	
170M5463			700		405000	
170M5464			800		575000	
170M5465			900		840000	
170M5466			1000		1250000	
170M5467	aR	2	1100	600	1600000	
170M5468			1250		2400000	
170M6458	aR	3	500	690	95000	
170M6459			550		135000	
170M6460			630		210000	
170M6461			700		300000	
170M6462			800		465000	
170M6463			900		670000	
170M6464			1000		945000	
170M6465			1100		1300000	
170M6466			1250		1950000	
170M6467			1400		2450000	
170M6468			1500		3100000	
170M6469			1600		3900000	
170M6470	aR	3	1800	600	5250000	
170M6471	aR	3	2000	550	6350000	

Fuse holders to suit High speed fuse links				
170H3003	To suit 80mm	630	1000	1
170H3004		1250	1000	
170H3005	To suit 110mm	630	1400	
170H3006		1250	1400	
170H0235	Micro switch	To suit Type 'T' Indicator		
170H0236		To suit Type 'K' Indicator		
170H0069		To suit Type 'K' Indicator		



170M5458



170M6462



170H3004

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series Glass tube fuse links

Item no.	Amp rating	Volts	Type		MOQ
M205 fuse links - 5 X 20mm.					
S500-(A)-R	32 to 10A	250	Glass	Fast	10
S506-(A)-R				T/Delay	
S501-(A)-R	32 to 10A	250	Ceramic	Fast	10
S505-(A)-R				T/Delay	



AGC

3AG fuse links - 6.3 X 32mm.
Fast-acting, glass tube
Optional axial leads available
1/4 x 1-1/4 (6.3mm x 32mm) physical size
Glass tube, nickel-plated brass endcap construction
UL Listed product meets standard 248-14

AGC-(A)	1/4 to 10A	250	Glass	Fast	5
	15 to 50A	32			

3AG fuse links - 6.3 X 32mm.
Time-delay
Optional axial leads available
1/4 x 1 1/4 (6.4 x 31.7mm) physical size
Glass tube, nickel-plated brass endcap construction
UL Listed product meets standard 248-14

MDL-(A)	1/4 to 8A	250	Glass	T/Delay	5
	15, 20, 25, 30, 35, 40, 50	32			



AGW

3AG fuse links - 6.3 X 32mm.

ABC-(A)	1/4 to 30A	250	Ceramic	Fast	5
MDA-(A)	1/4 to 30A			T/Delay	

1AG fuse links - 6.3 X 16mm.
Fast acting
1/4" x 5/8" (6.3mm x 15.9mm) physical size
Glass tube, nickel-plated brass endcap construction
Optional leaded version available
UL Listed product meets standard 248-14

AGA-(A)	630mA to 5A	250	Glass	Fast	5
	6 to 30A	32			



AGU

7AG fuse links - 6.3 X 22mm.
Fast-acting
1/4" x 7/8" (6.3 x 22.2mm) physical size
Glass tube, nickel-plated brass endcap construction
Mounts in inline holders HHB, HHH, HRK or 1/4" clips

AGW-(A)	1 to 30A	32	Glass	Fast	5

8AG fuse links - 6.3 X 25mm.

AGX-(A)	1/1 to 2A	250	Glass	Fast	5
	2.5 to 7A	125			
	8 to 30A	32			

5AG fuse links - 10.3 X 38mm.

AGU-(A)	1 to 3A	250	Glass	Fast	5
	4 to 30A	32			



HKP

Fuse holders.

HTC-55M	6.3	250	Panel mount	M205	1
HKP	30	250		3AG	

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series Surge protection

Eaton's Bussmann™ series one-pole IEC Class II modular surge arresters for TN and TT systems feature local easyID™ visual status indication and optional remote contact signaling. The unique module locking system fixes the protection module to the base.
System volts: 275, 320, 385, 440, 600

The unique nature of Photovoltaic (PV) installations make them vulnerable to damage from lightning strikes and overvoltage events. Bussmann® series DIN-Rail PV Surge Protection Devices (SPDs) combine surge and lightning protection for complete PV protection from overvoltage events.
PV SPD with integrated overcurrent protection ensures complete device isolation for enhanced system safety

Item no.	Description	Applic	Volts	Poles	Box qty
Surge protection.					
BSPM1275TN	Without remote signalling	Indust Class II	275Vac	1	1
BSPM1275TNR	With remote signalling				
BSPM1375TN	Without remote signalling		275Vac	3	1
BSPM1375TNR	With remote signalling				
BPM275IEC	Replacement module		275Vac	1	1
BSPS3255TNC	Without remote signalling	Indust Class 1	275Vac	3	1
BSPS3255TNCR	With remote signalling				
BPS255IEC	Replacement module				
BSPH31000YPV	Without remote signalling	Solar	1000Vdc	1	1
BSPH31000YPVR	With remote signalling				
BSPS31000YPV	Without remote signalling				
BPH500YPV	Replacement module (outer)				
BPM500YPV	Replacement module (inner)				



BSPM1275TN

Bussmann series fuse kits

Item no.	Description
NO-140	3AG fuses, glass, fast & time delay, 140pcs
NO-220	M205 fuses, glass, fast & time delay, 220pcs
NO-270	3AG & M205 fuses, glass, fast & time delay, 270pcs
GSK-260	3AG & M205 fuses, glass & ceramic, fast & time delay, 260pcs

Bussmann series automotive

Item no.	Amp rating	Volts	Type		MOQ
Automotive Blade Fuses The ATL, ATR, ATM, ATC and MAX blade fuses are commonly used in most domestic and imported cars today. All Bussmann blade fuses meet or exceed OEM and SAE standards					
ATM-(A)	2, 3, 4, 5, 7.5, 10, 15, 20, 25, 30	32	Fast	Mini	5
ATM-(A)LP	5, 7.5, 10, 15, 20, 25, 30	32	Fast	Lo Profile	5
ATC-(A)	1, 2, 3, 4, 5, 7.5, 10, 15, 20, 25, 30, 40	32	Fast	Std	5
MAX-(A)	20, 30, 40, 50, 60, 70, 80	32	Fast	Large	1
AMI-(A)	100-300A	32			
AMG-(A)	50-100A				
HMID	Fuseholder to suit AMI				1
HMEG	Fuseholder to suit AMG				1
Automative Low-Voltage Limiter					
ANL (A)	35, 40, 50, 60, 100, 130, 150	32	Non Delay		1
	175, 200, 225, 250, 275				
	300, 325, 350, 400, 500				
ANN (A)	10, 35, 40, 50, 60, 100, 130, 150, 175, 200, 225, 250, 275, 300	32	Very Fast		1
	325, 350, 400, 500, 600, 675, 700, 800				
4164	Fuse Base to Suit ANL & ANN				1



ATM-(A)



MAX-(A)



ANL (A,

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series solar products.

Bussmann series solar products.

Eaton's Bussmann series range of 14 x 51 mm package fuse links is specifically designed for protecting an isolating photovoltaic strings. These fuse links are capable of interrupting low overcurrents associated with faulted PV systems (reverse current, multi array fault).

Rated voltage: 1000 V d.c. (25 and 32 A)
1100 V d.c. (15 and 20 A)

Rated current: 15 to 32 A

Breaking capacity: 10 kA

Operating class: gPV and UL PV fuse links



CHPV2U

Item no.	Description	Body dim	Amps	Volts	Box qty
Photovoltaic fuse links - ferrule fuse holders.					
CHPV1U	With indicator	10 X 38mm	30	1000 Vdc	12
CHPV2U					6
CHPV1IU		10 X 38mm	30	1000	12
CHPV2IU					6
CH141D-PV		10 X 38mm	30	1000 Vdc	6



PV-1A10F

Photovoltaic fuse links					
PV-1A10F	Solar fuse - ferrule	10 X 38mm	1	1000 Vdc	10
PV-2A10F			2		
PV-3A10F			3		
PV-4A10F			4		
PV-5A10F			5		
PV-6A10F			6		
PV-8A10F			8		
PV-10A10F			10		
PV-12A10F			12		
PV-15A10F			15		
PV-20A10F			20		
PV-15A14F	Solar fuse - ferrule	14 X 51mm	15		
PV-20A14F			20		
PV-25A14F			25		
PV-32A14F			32		
PV-15A14LF	Solar fuse - ferrule	14 X 65mm	15	1300 Vdc	10
PV-20A14LF			20		
PV-25A14LF			25		
PV-32A14LF			32		



SD2-D-PV

Item no.	Description	Amps	Volts	Poles	Box qty
Photovoltaic fuse links - blade fuse holders.					
SD1-D-PV	For PV-NH1	250	1500 Vdc	1	1
SD2-D-PV	For PV-NH2	400			1
SD3-D-PV	For PV-NH3	630			1
SD1XL-S	For 01 & 1XL	250			1
SD2XL-S	For 2XL	400			1
SD3L-S	For 3L	630			1

Downloaded from Arrow.com.

LV Fuse gear

Bussmann series solar products.

Bussmann series solar products.

Eaton's Bussmann series NH size and XL package photovoltaic fuse links are specifically designed to protect and isolate photovoltaic array combiners and disconnects. These fuse links are capable of interrupting low overcurrents associated with faulted PV systems (reverse current, multi-array fault).

Rated voltage: NH - 1000 V d.c.
XL - 1000, 1100, 1200, 1500 V d.c.

Rated current: NH - 32 to 400 A
XL - 50 to 600 A

Breaking capacity: NH - 50 kA
XL - 1000 V d.c. (Size 01 and 3: 50kA, Size 1 and 2: 33kA)
1500 V d.c. : 30kA

Operating class: gPV and UL PV fuse links

Item no.	Description	Amps	Volts	Body size	Box qty
Photovoltaic fuse links.					
PV-32ANH1	Solar fuse - blade	32	1000 Vdc	1	1
PV-40ANH1		40			
PV-50ANH1		50			
PV-63ANH1		63			
PV-80ANH1		80			
PV-100ANH1		100			
PV-125ANH1		125			
PV-160ANH1		160			
PV-63A-01XL	Solar fuse - blade	50	1000 Vdc	01	1
PV-80A-01XL		63			
PV-100A-01XL		80			
PV-125A-01XL		100			
PV-160A-01XL		125			
PV-200A-1XL	Solar fuse - blade	200	1000 Vdc	1	1
PV-160A-2XL	Solar fuse - blade	160	1000 Vdc	2	1
PV-200A-2XL		200			
PV-250A-2XL		250			
PV-315A-2XL		315			
PV-355A-2XL		355			
PV-350A-3L	Solar fuse - blade	350	1000 Vdc	3	1
PV-400A-3L		400			
PV-500A-3L		500			
PV-600A-3L		600			
PV-63A-01XL-D	Solar fuse - bolted	63	1000 Vdc	01	
PV-80A-01XL-D		80			
PV-100A-01XL-D		100			
PV-125A-01XL-D		125			
PV-160A-01XL-D		160			
PV-200A-1XL-D	Solar fuse - bolted	100	1000 Vdc	1	
PV-160A-2XL-D	Solar fuse - bolted	160	1000 Vdc	2	
PV-200A-2XL-D		200			
PV-250A-2XL-D		250			
PV-315A-2XL-D		350			
PV-355A-2XL-D		400			
PV-350A-3L-D	Solar fuse - bolted	350	1000 Vdc		
PV-400A-3L-D		400			
PV-500A-3L-D		500			
PV-600A-3L-D		600			



PV-200ANH1



PV-250ANH2



PV-250ANH2-B



PV-250A2XL-D

Downloaded from Arrow.com.

MV Fuse gear

Bussmann series medium voltage fuse links.



Air Fuse Links

Standard: BS 2692-1
Rated voltage: 3.6 to 72.5kV
Rated current: 3.15 to 160A
Breaking capacity: Up to 40kA
Operating class: Back-up
Applications: Suitable for primary side transformer protection, fuse switch combination, unit fuse bases and fuse switches



24ADIHA25

Item no.	Amps	Volts	Lth	Dis	MOQ
Medium voltage fuse links for use in air.					
12BDGHA6.3	6.3	12kV	359	51	3
12BDGHA10	10				
12BDGHA16	16				
12BDGHA20	20				
12BDGHA25	25				
12BDGHA31.5	31.5				
12BDGHA40	40				
12BDGHA50	50				
12BFGHA63	63	12kV	359	76	3
12BFGHA71	71				
12BFGHA80	80				
12BFGHA90	90				
12BFGHA100	100				
12AKGHA125	125				
24ADIHA3.15	3.15	24kV	565	51	3
24ADIHA6.3	6.3				
24ADIHA10	10				
24ADIHA16	16				
24ADIHA20	20				
24ADIHA25	25				
24ADIHA31.5	31.5				
24AFIHA40	40	24kV	565	76	3
24AFIHA50	50				
24AFIHA63	63				
24AFIHA80	80				
24AFIHA90	90				



3.6ABWNA6.3

Medium voltage fuse links - VT for use in air.						
3.6ABWNA3.15	**AIR3.3/3**	3.15	3.6kV	142	25.4	1
3.6ABWNA6.3		6.3				
3.6ABCNA3.15		3.15	3.6kV	195	25.4	1
3.6ABCNA6.3		6.3				
3.6ABCNA10		10				
7.2VTDNN1		1	7.2Kv	142		1
7.2ABWNA3.15	**VTF6.6/3**	3.15			25.4	1
7.2ABWNA6.3		6.3			25.4	1
7.2VTDNN0.62		0.62				
7.2ABCNA3.15		3.15			25.4	1
7.2ABCNA6.3		6.3				
12VTDNN0.5	**VTF11/0.5**	0.5	12kV	195	25.4	1
12VTDNN1	**VTF11/1**	1				
12ABCNA3.15	**VTF11/3**	3.15				
24ABGNA3.15		3.15	24kV	359	25.4	1

Downloaded from Arrow.com.

MV Fuse gear

Bussmann series medium voltage fuse links.

Oil Fuse Links

Standard:	IEC 60282-1, BS 2692-1 and ESI Standard 12-8
Rated voltage:	3.6 to 24kV
Rated current:	6.3 to 250A
Breaking capacity:	Up to 50kA
Operating class:	Back-up
Applications:	Primary side transformer protection and oil filled switch combination unit
Other:	Fitted with a pyrotechnic striker for open fuse indication



Item no.		Amps	Volts	Lth	Dis	MOQ
Medium voltage fuse links for use in oil.						
12OEFMA6.3	**KEBXO5**	6.3	12kV	254	63.5	3
12OEFMA10	**KEBXO10**	10				
12OEFMA16	**KEBXO16**	16				
12OEFMA20	**KEBXO20**	20				
12OEFMA25	**KEBXO25**	25				
12OEFMA31.5		31.5				
12OEFMA40	**KEBXO40**	40				
12OEFMA50	**KEBXO50**	50				
12OEFMA63	**KEBXO63**	63				
12OHFMA71		71				
12OHFMA80	**KEBXO80**	80				
12OHFMA90		90				
12OHFMA100		100				
12OHGMA6.3	**KEMXO5**	6.3	12kV	359	63.5	3
12OHGMA10	**KEMXO10**	10				
12OHGMA16	**KEMXO16**	16				
12OHGMA20	**KEMXO20**	20				
12OHGMA25	**KEMXO25**	25				
12OHGMA31.5		31.5				
12OHGMA40	**KEMXO40**	40				
12OHGMA50	**KEMXO50**	50				
12OHGMA63	**KEMXO63**	63				
12OHGMA71		71				
12OHGMA80	**KEMXO80**	80				
12OHGMA90	**KEMXO90**	90				
12OHGMA100	**KEMXO100**	100				
12OLGMA125	**KEMXO120**	125				



120EFMA820

Medium voltage fuse links - VT for use in oil.						
	OIR6.6/0.62	0.62	7.2kV	142	22	1
7.2OBWNA3.15		3.15	7.2kV	142	25.4	1
7.2OBWNA6.3		6.3				
7.2OBCNA3.15	**OIR6.6/3**	3.15	7.2kV	195	25.4	1
7.2OBCNA6.3		6.3				
	OIR11/0.62	0.62	7.2kV		25.4	1
12OBCNA3.15		3.15	12kV	195	25.4	1
24OBGNA3.15		3.15	24kV	359	25.4	1
36OBGNA3.15		3.15	36kV			



7.20BCNA3.15

Downloaded from Arrow.com.

MV Fuse gear

Bussmann series medium voltage fuse links.



DIN Fuse Links

Standard:	DIN 43625, IEC 60282-1 and VDE 0670-4
Rated voltage:	3.6 to 36kV
Rated current:	6.3 to 400A
Breaking capacity:	20 to 63kA
Operating class:	Back-up
Applications:	Suitable for primary side transformer protection, fuse switch combination, unit fuse bases and fuse switches



12TDLEJ25



24TDMEJ20



3.6WDLSJ50

Item no.	Amps	Volts	Lth	Dis	MOQ
Medium voltage fuse links - DIN standard.					
12TDLEJ6.3	6.3	12kV	292	51	3
12TDLEJ10	10				
12TDLEJ16	16				
12TDLEJ20	20				
12TDLEJ25	25				
12TDLEJ31.5	31.5				
12TDLEJ40	40				
12TDLEJ50	50				
12TDLEJ63	63				
12THLEJ80	80	12kV	292	67	3
12THLEJ100	100				
12TKLEJ125	125	12kV	292	76	3
12TXLEJ160	160	12kV	292	88	3
12TXLEJ200	200				
24TDMEJ6.3	6.3	24kV	442	51	3
24TDMEJ10	10				
24TDMEJ16	16				
24TDMEJ20	20				
24TDMEJ25	25				
24TDMEJ31.5	31.5				
24TDMEJ40	40				
24TDMEJ50	50	24kV	442	67	3
24THMEJ63	63				
24THMEJ80	80				
24THMEJ100	100				
24TXMEJ125	125	24kV	442	88	3
24TXMEJ160	160				
Medium voltage fuse links - DIN motor start.					
3.6WDLSJ50	50	3.6kV	292	51	3
3.6WDLSJ63	63				
3.6WDLSJ80	80				
3.6WDLSJ100	100				
3.6WDLSJ125	125				
3.6WFLSJ160	160				
3.6WFLSJ200	200				
3.6WKLSJ250	250	3.6kV	292	76	3
3.6WKLSJ315	315				
3.6WKLSJ400	400				
7.2WFMSJ25	25	7.2kV	442	76	3
7.2WFMSJ31.5	31.5				
7.2WFMSJ40	40				
7.2WFMSJ50	50				
7.2WFMSJ63	63				
7.2WFMSJ80	80				
7.2WFMSJ100	100				
7.2WFMSJ125	125				
7.2WFMSJ160	160				
7.2WKMSJ200	200				
7.2WKMSJ224	224				
7.2WKMSJ250	250				
7.2WKMSJ315	315				

Downloaded from Arrow.com.

MV Fuse gear

Bussmann series medium voltage fuse links.

Motor Start Fuse Links

Standard:	IEC 60282-1, DIN 43625 and BS 2692
Rated voltage:	2.75 to 7.2kV
Rated current:	6.3 to 400A
Breaking capacity:	Up to 63kA
Operating class:	Back-up
Applications:	Provide short-circuit protection in motor circuits to both the motor starter & cables
Other:	Fitted with a pyrotechnic striker for open fuse indication



Item no.		Amps	Volts	Lth	Dis	MOQ
Medium voltage fuse links - BS motor start.						
3.6WDFHO50		50				
3.6WDFHO63		63				
3.6WDFHO80		80	3.6kV	254a	51	3
3.6WDFHO100	**K81PEX100**	100				
3.6WDFHO125	**K81PEX125**	125				
3.6WFFHO160	**K81PEX160**	160				
3.6WFFHO200	**K81PEX200**	200				
3.6WKFHO250	**K81PEX250**	250				
3.6WKFHO315	**K81PEX315**	315	3.6kV	254a	76	3
3.6WKFHO355	**K81PEX350**	355				
3.6WKFHO400		400				
	K81PRX450	450				
3.6WDFHO50		50				
3.6WDFHO63		63				
3.6WDFHO80		80	3.6kV	254a	51	3
3.6WDFHO100	**K81PEX100**	100				
3.6WDFHO125	**K81PEX125**	125				
3.6WFFHO160	**K81PEX160**	160				
3.6WFFHO200	**K81PEX200**	200				
3.6WKFHO250	**K81PEX250**	250				
3.6WKFHO315	**K81PEX315**	315	3.6kV	254a	76	3
3.6WKFHO355	**K81PEX350**	355				
3.6WKFHO400		400				
	K81PRX450	450				
7.2WFNHO25		25				
7.2WFNHO31.5		31.5				
7.2WFNHO40		40				
7.2WFNHO50	**K81SDX50**	50				
7.2WFNHO63	**K81SDX63**	63				
7.2WFNHO80	**K81SDX80**	80				
7.2WFNHO100	**K81SDX100**	100	7.2kV	403	76	3
7.2WFNHO125	**K81SDX125**	125				
7.2WFNHO160	**K81SDX160**	160				
7.2WKNHO200	**K81SDX200**	200				
7.2WKNHO224	**K81SDX225**	224				
7.2WKNHO250	**K81SDX250**	250				
7.2WKNHO315	**K81SDX315**	315				



3.6WKFHO250



7.2WFNHO125

Item no.	Description	MOQ
Medium voltage fuse links - mounting clips.		
1A1873	To Suit 20mm	
A3354705	To Suit 25.4mm	
A3354710	To Suit 51.0mm	
A3354720	To Suit 63.5mm	2
A3354730	To Suit 76.0mm	
A3354745	To Suit 45mm DIN	
270303	To Suit 45mm DIN	



Mounting clips

Downloaded from Arrow.com.