
42575 -3 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



42575 -3

Active

Taper Pins and Blocks

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Taper Pins
- Pin Type = Solid
- Pin Style = Standard
- 53 Series
- Loose Piece

View all Features | Find Similar Products

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- PIN, TAPER, "53" SERIES PIDG (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- Contact, TAYP -AIR Pins and Blocks (PDF, English)
- Contact, Taper Pins (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- Taper Pin Crimping Dies for AMPORTAMATIC Crimping Tool (PDF, English)

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Taper Pins
- Insulation Support = Pre -Insulated
- Insulation Diameter (mm [in]) = 1.52 – 2.54 [0.060 – 0.100]
- Finish = Gold (30)
- Comment = For Stranded Wire Only.

Body Related Features:

- Pin Type = Solid
- Pin Style = Standard
- Series = 53
- Wire Range (mm [AWG]) = 0.50 -0.90 ² [20-18]
- Insulation Color = Natural
- Overall Length (mm [in]) = 18.16 [0.715]
- Mates With = 53 Series Connector Block

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- Brand = AMP

© 2008 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.