

Part Number : [190710225](#)


Product Description : InsulKrimp Ring Tongue
Terminal for 6 AWG Wire, Carton

Series Number : 19071

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : E-660-14X



Documents and Resources

Drawings

[190710225_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19902-009-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19071
Description	InsulKrimp Ring Tongue Terminal for 6 AWG Wire, Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Style	Ring
Type	Ring Terminal
UPC	800753071858

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	5.425/g

Packaging Type	Carton
Stud Size	1/4" (M6)
Wire Insulation Diameter	11.20mm max.
Wire Size (AWG)	6

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Crimp Tool Kit for 6 AWG Insulated Ring Terminals	<u>640017770</u>

This document was generated on Apr 23, 2026