








PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	TIN LEAD	TIN LEAD	TIN LEAD	TIN LEAD	LEAD FREE	LEAD FREE	LEAD FREE
09	30.81	24.99	16.96	16.79	10.96	D09P91C4P V00	D09P91C6P V00	D09P91C8P V00	D09P91C8P V00LF	D09P91C4P V00LF	D09P91C6P V00LF	D09P91C8P V00LF
15	39.14	33.32	25.18	25.12	19.18	D15P91C4P V00	D15P91C6P V00	D15P91C8P V00	D15P91C8P V00LF	D15P91C4P V00LF	D15P91C6P V00LF	D15P91C8P V00LF
25	53.03	47.04	39.12	38.84	33.12	D25P91C4P V00	D25P91C6P V00	D25P91C8P V00	D25P91C8P V00LF	D25P91C4P V00LF	D25P91C6P V00LF	D25P91C8P V00LF
37	69.32	63.50	55.68	55.30	49.68	D37P91C4P V00	D37P91C6P V00	D37P91C8P V00	D37P91C8P V00LF	D37P91C4P V00LF	D37P91C6P V00LF	D37P91C8P V00LF
						gold flash	0.76» gold	1.25» gold		gold flash	0.76» gold	1.25» gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com				surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 							
				TOLERANCES UNLESS OTHERWISE SPECIFIED													
				ANGULAR		LINEAR		0.X		±0.1		size A3		Scale 2			
Dr	PESSON	1992-09-15	Eng	PESSON	1992-09-15	Chr	NIRMAL GEORGE	2009-11-24	Appr	SUDHIR VARMA	2009-11-24	Product family		D-SUB		Spec ref -	
rev	ecn no	dr	date														
G	-	MAS	2000/08/24														
H	LS05-004	LMA	2004/12/31														
J	LS06-0097	LGO	2006/07/29														
K	LS06-0140	LGO	2006/09/22														
L	109-0268	NG	2009-11-24														
-	-	-	-														
-	-	-	-														

		MALE CONNECTOR DELTA D		EUROPE STRAIGHT PRESS-FIT		Rev.			
catalog no		-		dwg no		C01-8646-0112		L	
CUSTOMER		sheet 1 of 1		-		-		-	

