

Representative Image

Catalog No. TC5345A

Description: 4WAY MTG BASE 1.13X1.13IN NAT NYL A

UPC No 786210872247

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Four-Way Adhesive Mounting Base, Natural Nylon 6.6 for Temperatures up to 66 Degrees Celsius (150 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Self-Adhesive Mounting Method, 100 Pack

Descriptors

Category	Cable tie mounts
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

Specifications

Number Of Entries	4
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

Classifications

Brand Name	Ty-Rap

Dimensions

Mount Size	#6

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.