**Part Number :** 1300940361
**Product Description :** Standard Duty Support Grip, Locking Bale, Split Lace, Single Weave, Cable Diameter 50.80-63.25mm (2.000-2.490"), Approximate Break Strength 1524.07kg (3360 lbs)
**Series Number :** 130094
**Status :** Active
**Product Category :** Cable Grips
**Engineering Part Number :** 35232



## Documents and Resources

### Drawings

PK-130227-004-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Cable Grips |
| Series | 130094 |
| Description | Standard Duty Support Grip, Locking Bale, Split Lace, Single Weave, Cable Diameter 50.80-63.25mm (2.000-2.490"), Approximate Break Strength 1524.07kg (3360 lbs) |
| Product Name | Standard Duty |
| Type | Support Grip |
| UPC | 78678835232 |

### Agency

| | |
|---|---|
| CSA | LR32159 |

### Physical

| | |
|---|---|
| Approximate Break Strength | 1524.07kg (3360 lbs) |
| Bale Length | 0.457m (18.00") |
| Body Style | Straight |
| Cable Diameter | 50.80-63.25mm (2.000-2.490") |
| Color - Grommet | N/A |
| Eye Type | Locking Bale |
| Gender | N/A |
| Material - Body | N/A |
| Material - Grip | Non-magnetic Tin Bronze Wire |
| Mesh Length | 0.559m (22.00") |
| Number of Holes | N/A |
| O-Ring | N/A |
| Thread Size | N/A |

Downloaded from Arrow.com.

This document was generated on Dec 25, 2025

Downloaded from Arrow.com.