



Part Number : 1301050057

Series Number : 130105

Product Category : Lamps and Lights

Product Description : Watertite Wet Location
30W 12V Spotlight with Screw Release Guard,
14/2 SOOW, Overall Length 15.24m (50.0')

Status : Active

Engineering Number : 1647-12

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130105

Description	Watertite Wet Location 30W 12V Spotlight with Screw Release Guard, 14/2 SOOW, Overall Length 15.24m (50.0')
NEMA Configuration	Non-NEMA
Product Family	Specialty Lighting
Product Name	Watertite
Type	Hand Lamps, Specialty Light
UPC	78678862521

Agency

CSA	E59049
UL	E59049

Electrical

Lamp Wattage - Maximum	30W
Lumens	300
On/Off Switch	No
Voltage (Fixture) - Maximum	12V AC/DC

Physical

Bulb Type	Quartz Halogen
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Secondary	14/2 SOOW
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	457.20mm (18.000")
Lamp Type	PAR36
Length	N/A
Material - Guard	#10 Gauge Vinyl Coated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Jul 03, 2024