



HD10 Series Housing for Male Terminals - 6 Cavities, In-Line, Threaded Rear

COM-15810 ROHS ✓

DESCRIPTION

FEATURES

DOCUMENTS

- Connector Style : Housing for male terminals
- Connector System : Wire-to-Wire
- Sealable : Yes
- Hybrid Connector : No
- Primary Locking Feature : Integrated in Housing
- Number of Positions : 6
- Nominal Voltage Architecture (V): 12, 24, 42, 48, 80, 90, 125, 240
- Mating Pin Diameter : 1.5 mm [.059 in]

images are CC BY 2.0



COMMENTS 0

REVIEWS 0

Comments

Looking for answers to technical questions?

We welcome your comments and suggestions below. However, if you are looking for solutions to technical questions please see our [Technical Assistance](#) page.

Log in or register to post comments.



Email address

SUBSCRIBE TO NEWSLETTER

ABOUT SPARKFUN

Read Our Story
Press & Media
SparkFun Education
Job Openings

PARTNER WITH US

See Our Partners
Become a Distributor/Reseller
Receive Volume Discounts
Build a Custom Kit
Apply for a Hardware Donation

SUPPORT

Customer Support
Purchase Orders & Payment
Terms
Technical Assistance
FAQs
Contact Us

SITE INFORMATION

Terms of Service
Privacy Policy
Compliance
Site Map

SparkFun Electronics ® / 6333 Dry Creek Parkway, Niwot, Colorado 80503