
Part Number : 1300130396
Product Description : Mini-Change Receptacle, 4 Poles, Panel Mount, PG 13.5 Threads, Male (Straight) to 18 AWG Leads, Length 0.305m (1.0')
Series Number : 130013
Status : Active
Product Category : Circular Industrial Connectors
Engineering Part Number : 1R4D06A16A120



Documents and Resources

Drawings

1300130396_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130013
Description	Mini-Change Receptacle, 4 Poles, Panel Mount, PG 13.5 Threads, Male (Straight) to 18 AWG Leads, Length 0.305m (1.0')
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	78678844585

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	5.6A
Voltage - Maximum	300V AC/DC

Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	0.305m
Material - Component	Zinc Die-Cast with Black Epoxy
Mounting Thread Size	PG13.5
Net Weight	55.940/g
Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-20° to +105°C

Downloaded from Arrow.com.

Wire/Cable Type	UL 1061
Wire Size (AWG)	18

Downloaded from Arrow.com.