








A						Det.	Name	 All Dim. in mm Orig. Size DIN A 4	D-sub, High temperature, 9 poles, female, straight, with solder pins 2.9, and screw lock.	Maßstab/ Scale 1,5:1
						Detail.	05-MAR-02			
						Insp.				
						Stand.				
	09 66 115 3503	4-40 UNC	1					 HARTING	TB 09 66 115 x50x	Blatt/ Page 3
	09 66 115 6503	4-40 UNC	2	31892	05/05/04	JH				
	09 66 115 7503	4-40 UNC	3	29723	05-MAR-02	CV				
	Part number	Screw lock thread	Performance level	Mod.	Det.	Name	HARTING EURL F-95972 Paris			