

SHIELD-KON® two-part screen connector

SHIELD-KON® two-part screen connector for connecting screened cables, inner sleeve GSB, outer sleeve GSC, reliable connection

Info

Consists of inner and outer sleeve



Rail



Interference signals

Benefits

A hard, stable inner sleeve absorbs the pressure and protects the conductor on the inside from mechanical stress
Hexagonal shaped crimping of the soft outer sleeve guarantees a perfect electrical and mechanical connection

Application range

For screen cables with a dielectric diameter from 1.1 to 9,4 mm (diameter after removing the screen)
Telecommunication
Railway applications

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002650

ETIM 5.0 Class-Description: Connection for screened wires

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002650

ETIM 6.0 Class-Description: Connection for screened wires

Material:

Bronze

Galvanically galvanized

Temperature range:

Temperature shock test

100 cycles of temperature changes between -40°C and

+155°C produced a negligible change in the contact resistance.

Note

SHIELD-KON® is a registered trademark of ABB.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SHIELD-KON® two-part screen connector

Article number	Article designation	Colour	Inner x outer sleeve Ø (mm)	Suitable crimp insert	Nest	Pieces / PU
Inner sleeves						
61749430	GSB 046	silver	1.17 x 1.9	-	-	100
61749440	GSB 058	yellow	1.47 x 2.1	-	-	100
61749450	GSB 063	red	1.6 x 2.23	-	-	100
61749460	GSB 071	green	1.87 x 2.44	-	-	100
61749470	GSB 080	blue	2 x 2.63	-	-	100
61749480	GSB 090	orange	2.2 x 2.9	-	-	100
61749490	GSB 096	purple	2.44 x 3.02	-	-	100
61749500	GSB 101	yellow	2.56 x 3.16	-	-	100
61749510	GSB 109	red	2.76 x 3.36	-	-	100
61749520	GSB 115	silver	2.92 x 3.7	-	-	100
61749530	GSB 124	green	3.14 x 3.68	-	-	100
61749540	GSB 128	silver	3.25 x 3.86	-	-	100
61749550	GSB 134	orange	3.4 x 4	-	-	100
61749560	GSB 149	blue	3.78 x 4.54	-	-	100
61749570	GSB 156	red	3.96 x 4.9	-	-	100
61749580	GSB 165	silver	4.2 x 4.92	-	-	100
61749590	GSB 175	green	4.44 x 5.46	-	-	100
61749600	GSB 187	yellow	4.75 x 5.76	-	-	100
61749610	GSB 194	blue	4.93 x 5.76	-	-	100
61749620	GSB 205	orange	5.2 x 6.22	-	-	100
61749630	GSB 219	silver	5.56 x 6.35	-	-	100
61749640	GSB 225	yellow	5.71 x 6.5	-	-	100
61749650	GSB 232	red	5.9 x 6.7	-	-	100
61749660	GSB 250	green	6.35 x 7.14	-	-	100
61749670	GSB 261	blue	6.63 x 7.54	-	-	100
61749680	GSB 266	silver	6.75 x 7.54	-	-	100
61749690	GSB 275	orange	6.98 x 7.77	-	-	100
61749700	GSB 281	yellow	7.14 x 8.4	-	-	100
61749710	GSB 287	silver	7.29 x 8.3	-	-	100
61749720	GSB 297	red	7.54 x 8.5	-	-	100
61749730	GSB 312	purple	7.92 x 9.2	-	-	100
61749740	GSB 348	orange	8.84 x 10.2	-	-	100
61749750	GSB 375	blue	9.52 x 10.3	-	-	100

Last Update (05.09.2020)
 ©2020 Lapp Group - Technical changes reserved
 Product Management www.lappkabel.de
 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16

SHIELD-KON® two-part screen connector

Article number	Article designation	Colour	Inner x outer sleeve Ø (mm)	Suitable crimp insert	Nest	Pieces / PU
Outer sleeves						
61749810	GSC 101	silver	2.56 x 3.16	PEW 12.1425 SK	19	100
61749820	GSC 128	blue	3.25 x 3.86	PEW 12.1425 SK	00	100
61749830	GSC 149	purple	3.78 x 4.54	PEW 12.1425 SK	01	100
61749840	GSC 156	yellow	3.96 x 4.9	PEW 12.1425 SK	02	100
61749850	GSC 175	blue	4.4 x 5.46	PEW 12.1425 SK	03	100
61749860	GSC 187	orange	4.75 x 5.76	PEW 12.1426 SK	6	100
61749870	GSC 194	red	4.93 x 5.79	PEW 12.1426 SK	6	100
61749880	GSC 199	silver	5.05 x 5.97	PEW 12.1426 SK	6	100
61749890	GSC 205	yellow	5.2 x 6.22	PEW 12.1426 SK	8	100
61749900	GSC 219	green	5.56 x 6.35	PEW 12.1426 SK	8	100
61749910	GSC 225	purple	5.71 x 6.5	PEW 12.1426 SK	9	100
61749920	GSC 232	orange	5.9 x 6.7	PEW 12.1426 SK	10	100
61749930	GSC 261	yellow	6.63 x 7.54	PEW 12.1427 SK	11	100
61749940	GSC 275	silver	6.98 x 7.77	PEW 12.1427 SK	12	100
61749950	GSC 281	purple	7.14 x 8.4	PEW 12.1427 SK	14	100
61749960	GSC 287	blue	7.29 x 8.3	PEW 12.1427 SK	14	100
61749970	GSC 297	green	7.54 x 8.5	PEW 12.1427 SK	14	100
61749980	GSC 312	yellow	7.95 x 9.2	PEW 12.1428 SK	15	100
61749990	GSC 327	silver	8.3 x 9.45	PEW 12.1428 SK	16	100
61750000	GSC 348	orange	8.84 x 9.98	PEW 12.1428 SK	17	100
61750010	GSC 359	purple	9.12 x 10.13	PEW 12.1429 SK	50	100
61750020	GSC 375	yellow	9.52 x 10.3	PEW 12.1429 SK	51	100
61750030	GSC 405	red	10.28 x 11.5	PEW 12.1430 SK	52	100
61750040	GSC 415	blue	10.54 x 11.76	PEW 12.1430 SK	52	100
61750050	GSC 425	silver	10.8 x 12.06	PEW 12.1430 SK	54	100
61750060	GSC 460	silver	11.68 x 12.95	PEW 12S.1440 SK	56	100
61750070	GSC 500	green	12.7 x 14.6	PEW 12S.1440 SK	57	100

Last Update (05.09.2020)
 ©2020 Lapp Group - Technical changes reserved
 Product Management www.lappkabel.de
 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03.16